

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641280

Luminaire Tested: ML5612LSVWFL7597FS1E - 592W - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 592W - 1200LM - 5000K
Description: ML56 RR, 75D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1619.1 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641280

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641280

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92																																				
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84																																				
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76																																				
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70																																				
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																																				
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	58																																				
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54																																				
8	74	63	57	52	73	63	56	52	62	56	52	61	55	51	59	55	51	50																																				
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46																																				
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88051
5°	89338
10°	92054
15°	95570
20°	96726
25°	92180
30°	82922
35°	66977
40°	45476
45°	23634
50°	14381
55°	9510
60°	4973
65°	2802
70°	2770
75°	2745
80°	2728
85°	2717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23634 cd/sqm



TEST NUMBER: P641280

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.3	6.7
10°-20°	329.5	20.4
20°-30°	482.0	29.8
30°-40°	425.1	26.3
40°-50°	180.8	11.2
50°-60°	62.8	3.9
60°-70°	17.9	1.1
70°-80°	9.5	0.6
80°-90°	3.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	919.8	56.8
0°-40°	1344.9	83.1
0°-60°	1588.4	98.1
0°-90°	1619.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1619.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1115	
5°	1127	108
15°	1169	330
25°	1058	482
35°	695	425
45°	212	181
55°	69	63
65°	15	18
75°	9	9
85°	3	3
90°	0	



TEST NUMBER: P641280

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1115.4
2.5°	1118.4
5°	1127.4
7.5°	1137.9
10°	1148.4
12.5°	1158.9
15°	1169.4
17.5°	1169.4
20°	1151.4
22.5°	1113.9
25°	1058.3
27.5°	990.8
30°	909.7
32.5°	807.6
35°	695.0
37.5°	565.9
40°	441.3
42.5°	313.7
45°	211.7
47.5°	147.1
50°	117.1
52.5°	90.1
55°	69.1
57.5°	49.5
60°	31.5
62.5°	22.5
65°	15.0
67.5°	13.5
70°	12.0
72.5°	10.5
75°	9.0
77.5°	7.5
80°	6.0
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)