

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641287

Luminaire Tested: ML5612LSVWFL7597FS1E - 592W - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641287
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 592W - 900LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1209.7 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641287
CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641287

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	58	58	58	58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	61	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65781
5°	66746
10°	68776
15°	71404
20°	72263
25°	68871
30°	61957
35°	50044
40°	33976
45°	17650
50°	10746
55°	7102
60°	3726
65°	2092
70°	2077
75°	2044
80°	2046
85°	1993

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17650 cd/sqm



TEST NUMBER: P641287

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	6.7
10°-20°	246.2	20.4
20°-30°	360.1	29.8
30°-40°	317.6	26.3
40°-50°	135.1	11.2
50°-60°	46.9	3.9
60°-70°	13.4	1.1
70°-80°	7.1	0.6
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.2	56.8
0°-40°	1004.8	83.1
0°-60°	1186.8	98.1
0°-90°	1209.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	833	
5°	842	81
15°	874	246
25°	791	360
35°	519	318
45°	158	135
55°	52	47
65°	11	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P641287
CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	833.3
2.5°	835.6
5°	842.3
7.5°	850.1
10°	858.0
12.5°	865.8
15°	873.7
17.5°	873.7
20°	860.2
22.5°	832.2
25°	790.7
27.5°	740.2
30°	679.7
32.5°	603.4
35°	519.3
37.5°	422.8
40°	329.7
42.5°	234.4
45°	158.1
47.5°	109.9
50°	87.5
52.5°	67.3
55°	51.6
57.5°	37.0
60°	23.6
62.5°	16.8
65°	11.2
67.5°	10.1
70°	9.0
72.5°	7.9
75°	6.7
77.5°	5.6
80°	4.5
82.5°	3.4
85°	2.2
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)