

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641288

Luminaire Tested: ML5612LSVWFL7597FS1E - 592W - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 592W - 900LM - 3500K
Description: ML56 RR, 75D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1242.7 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641288

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P641288

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 99 | 100 | 98 | 96 | 96 | 95 | 94 | 92 | 92 | 92 | 92 |
| 2 | 106 | 101 | 96 | 92 | 104 | 99 | 95 | 91 | 96 | 92 | 89 | 93 | 90 | 87 | 90 | 87 | 85 | 84 | 84 | 84 | 84 |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 89 | 84 | 81 | 86 | 82 | 79 | 84 | 81 | 78 | 76 | 76 | 76 | 76 |
| 4 | 94 | 85 | 79 | 74 | 92 | 84 | 78 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 74 | 71 | 70 | 70 | 70 | 70 |
| 5 | 88 | 79 | 72 | 68 | 87 | 78 | 72 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 65 | 64 | 64 | 64 | 64 |
| 6 | 83 | 73 | 66 | 62 | 82 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 60 | 58 | 58 | 58 | 58 |
| 7 | 78 | 68 | 61 | 57 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 55 | 54 | 54 | 54 | 54 |
| 8 | 74 | 63 | 57 | 52 | 73 | 63 | 56 | 52 | 62 | 56 | 52 | 61 | 55 | 51 | 59 | 55 | 51 | 50 | 50 | 50 | 50 |
| 9 | 70 | 59 | 53 | 48 | 69 | 59 | 52 | 48 | 58 | 52 | 48 | 57 | 51 | 48 | 56 | 51 | 48 | 46 | 46 | 46 | 46 |
| 10 | 66 | 55 | 49 | 45 | 65 | 55 | 49 | 45 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 48 | 44 | 43 | 43 | 43 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 67573 |
| 5° | 68561 |
| 10° | 70644 |
| 15° | 73349 |
| 20° | 74237 |
| 25° | 70744 |
| 30° | 63643 |
| 35° | 51403 |
| 40° | 34903 |
| 45° | 18130 |
| 50° | 11041 |
| 55° | 7294 |
| 60° | 3821 |
| 65° | 2148 |
| 70° | 2123 |
| 75° | 2105 |
| 80° | 2091 |
| 85° | 2083 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18130 cd/sqm



TEST NUMBER: P641288

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 900LM - 3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 83.1 | 6.7 |
| 10°-20° | 252.9 | 20.4 |
| 20°-30° | 369.9 | 29.8 |
| 30°-40° | 326.3 | 26.3 |
| 40°-50° | 138.7 | 11.2 |
| 50°-60° | 48.2 | 3.9 |
| 60°-70° | 13.8 | 1.1 |
| 70°-80° | 7.3 | 0.6 |
| 80°-90° | 2.5 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 705.9 | 56.8 |
| 0°-40° | 1032.2 | 83.1 |
| 0°-60° | 1219.1 | 98.1 |
| 0°-90° | 1242.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1242.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 856 | |
| 5° | 865 | 83 |
| 15° | 898 | 253 |
| 25° | 812 | 370 |
| 35° | 533 | 326 |
| 45° | 162 | 139 |
| 55° | 53 | 48 |
| 65° | 12 | 14 |
| 75° | 7 | 7 |
| 85° | 2 | 3 |
| 90° | 0 | |



TEST NUMBER: P641288

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592W - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 856.0 |
| 2.5° | 858.3 |
| 5° | 865.2 |
| 7.5° | 873.3 |
| 10° | 881.3 |
| 12.5° | 889.4 |
| 15° | 897.5 |
| 17.5° | 897.5 |
| 20° | 883.7 |
| 22.5° | 854.8 |
| 25° | 812.2 |
| 27.5° | 760.4 |
| 30° | 698.2 |
| 32.5° | 619.8 |
| 35° | 533.4 |
| 37.5° | 434.3 |
| 40° | 338.7 |
| 42.5° | 240.8 |
| 45° | 162.4 |
| 47.5° | 112.9 |
| 50° | 89.9 |
| 52.5° | 69.1 |
| 55° | 53.0 |
| 57.5° | 38.0 |
| 60° | 24.2 |
| 62.5° | 17.3 |
| 65° | 11.5 |
| 67.5° | 10.4 |
| 70° | 9.2 |
| 72.5° | 8.1 |
| 75° | 6.9 |
| 77.5° | 5.8 |
| 80° | 4.6 |
| 82.5° | 3.5 |
| 85° | 2.3 |
| 87.5° | 1.2 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)