

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641803

Luminaire Tested: ML5612LSVWFL97FS1E - 692W - 1200LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641803  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-108)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 692W - 1200LM - 3500K  
Description: ML56 RR, MILKY OPTIC, 6" WHITE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1413.6 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.2  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641803  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 1200LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P641803

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 1200LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89																			
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79																			
3	96	88	81	76	94	87	80	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63																			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	53	48	59	53	48	58	52	48	57	51	47	46																			
8	69	57	49	44	67	56	49	44	55	48	44	54	48	44	53	47	43	42																			
9	64	52	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	59	48	42	37	47	41	37	47	41	37	46	40	37	35																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	44481
5°	44266
10°	43687
15°	42957
20°	42039
25°	40968
30°	39512
35°	37664
40°	33477
45°	25336
50°	17270
55°	11880
60°	8881
65°	7433
70°	6716
75°	6206
80°	5304
85°	4403

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25336 cd/sqm



TEST NUMBER: P641803

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 1200LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.1	5.4
10°-20°	213.1	15.1
20°-30°	311.1	22.0
30°-40°	347.5	24.6
40°-50°	252.9	17.9
50°-60°	116.3	8.2
60°-70°	58.0	4.1
70°-80°	30.5	2.2
80°-90°	8.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.4	42.5
0°-40°	947.9	67.1
0°-60°	1317.1	93.2
0°-90°	1413.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1413.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	811	
5°	804	76
15°	757	213
25°	677	311
35°	563	348
45°	327	253
55°	124	116
65°	57	58
75°	29	31
85°	7	8
90°	0	



TEST NUMBER: P641803

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 1200LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	811.4
2.5°	808.6
5°	804.4
7.5°	796.0
10°	784.8
12.5°	772.3
15°	756.9
17.5°	738.8
20°	720.6
22.5°	699.7
25°	677.3
27.5°	650.8
30°	624.2
32.5°	594.9
35°	562.8
37.5°	520.9
40°	467.8
42.5°	400.8
45°	326.8
47.5°	258.4
50°	202.5
52.5°	157.8
55°	124.3
57.5°	99.2
60°	81.0
62.5°	67.0
65°	57.3
67.5°	48.9
70°	41.9
72.5°	34.9
75°	29.3
77.5°	22.3
80°	16.8
82.5°	11.2
85°	7.0
87.5°	2.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)