

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641807

Luminaire Tested: ML5612LSVWFL97FS1E - 692W - 600LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641807  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-108)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 692W - 600LM - 3000K  
Description: ML56 RR, MILKY OPTIC, 6" WHITE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 886.1 lumens  
Efficiency: N/A  
Efficacy: 86.0 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.2  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641807

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 600LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641807

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 600LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89																			
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79																			
3	96	88	81	76	94	87	80	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	53	48	59	53	48	58	52	48	57	51	47	46																			
8	69	57	49	44	67	56	49	44	55	48	44	54	48	44	53	47	43	42																			
9	64	52	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	59	48	42	37	47	41	37	47	41	37	46	40	37	35																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27882
5°	27746
10°	27382
15°	26924
20°	26351
25°	25677
30°	24770
35°	23610
40°	20982
45°	15878
50°	10823
55°	7445
60°	5570
65°	4657
70°	4215
75°	3897
80°	3315
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15878 cd/sqm



TEST NUMBER: P641807

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 600LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.7	5.4
10°-20°	133.6	15.1
20°-30°	195.0	22.0
30°-40°	217.8	24.6
40°-50°	158.5	17.9
50°-60°	72.9	8.2
60°-70°	36.3	4.1
70°-80°	19.2	2.2
80°-90°	5.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.3	42.5
0°-40°	594.2	67.1
0°-60°	825.5	93.2
0°-90°	886.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	886.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	509	
5°	504	48
15°	474	134
25°	424	195
35°	353	218
45°	205	158
55°	78	73
65°	36	36
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P641807

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 600LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	508.6
2.5°	506.8
5°	504.2
7.5°	499.0
10°	491.9
12.5°	484.1
15°	474.4
17.5°	463.1
20°	451.7
22.5°	438.6
25°	424.5
27.5°	407.9
30°	391.3
32.5°	372.9
35°	352.8
37.5°	326.5
40°	293.2
42.5°	251.2
45°	204.8
47.5°	161.9
50°	126.9
52.5°	98.9
55°	77.9
57.5°	62.2
60°	50.8
62.5°	42.0
65°	35.9
67.5°	30.6
70°	26.3
72.5°	21.9
75°	18.4
77.5°	14.0
80°	10.5
82.5°	7.0
85°	4.4
87.5°	1.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)