

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641330

Luminaire Tested: ML5612LSVWFL7597FS1E - 593TBZB - 600LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-77)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 593TBZB - 600LM - 5000K
Description: ML56 RR, 75D TIR OPTIC, 5" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 998.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641330
CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593TBZB - 600LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641330

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593TBZB - 600LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																										
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																																				
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85																																				
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78																																				
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71																																				
5	89	80	74	69	88	79	73	69	77	72	68	76	71	67	74	70	67	65																																				
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60																																				
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55																																				
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51																																				
9	71	60	54	49	70	60	53	49	59	53	49	58	53	49	57	52	49	47																																				
10	67	56	50	46	66	56	50	46	55	49	46	54	49	45	53	49	45	44																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55890
5°	56714
10°	58452
15°	60706
20°	61586
25°	58628
30°	52632
35°	42219
40°	28401
45°	14033
50°	8191
55°	4927
60°	1674
65°	355
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14033 cd/sqm



TEST NUMBER: P641330

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593TBZB - 600LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	6.9
10°-20°	209.4	21.0
20°-30°	306.4	30.7
30°-40°	268.6	26.9
40°-50°	109.0	10.9
50°-60°	32.5	3.3
60°-70°	3.4	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.6	58.6
0°-40°	853.2	85.5
0°-60°	994.6	99.7
0°-90°	998.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	998.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	708	
5°	716	69
15°	743	209
25°	673	306
35°	438	269
45°	126	109
55°	36	32
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641330
CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593TBZB - 600LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	708.0
2.5°	709.9
5°	715.7
7.5°	722.5
10°	729.2
12.5°	736.0
15°	742.8
17.5°	743.7
20°	733.1
22.5°	708.0
25°	673.1
27.5°	629.6
30°	577.4
32.5°	513.6
35°	438.1
37.5°	355.9
40°	275.6
42.5°	192.5
45°	125.7
47.5°	85.1
50°	66.7
52.5°	49.3
55°	35.8
57.5°	23.2
60°	10.6
62.5°	5.8
65°	1.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)