

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641826

Luminaire Tested: ML5612LSVWFL97FS1E - 693BB - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-110)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 693BB - 900LM - 2700K
Description: ML56 RR, MILKY OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 845.7 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.21
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641826
CATALOG NUMBER: ML5612LSVWFL97FS1E - 693BB - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641826

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693BB - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91					91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83					83			
3	99	91	85	81	97	90	84	80	87	82	79	84	81	77	82	79	76	74					74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67					67			
5	86	77	70	64	85	76	69	64	74	68	63	72	67	63	70	66	62	61					61			
6	81	70	63	58	79	70	63	58	68	62	57	66	61	57	65	60	57	55					55			
7	76	65	58	53	74	64	57	53	63	57	52	61	56	52	60	55	52	50					50			
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46					46			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	43	42					42			
10	63	52	45	41	62	51	45	40	50	44	40	50	44	40	49	44	40	39					39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28824
5°	28753
10°	28601
15°	28292
20°	27938
25°	27449
30°	26656
35°	25404
40°	22249
45°	15730
50°	9117
55°	4693
60°	2149
65°	713
70°	176
75°	233
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15730 cd/sqm



TEST NUMBER: P641826

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693BB - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	5.9
10°-20°	140.6	16.6
20°-30°	208.6	24.7
30°-40°	233.8	27.6
40°-50°	157.1	18.6
50°-60°	47.9	5.7
60°-70°	7.1	0.8
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	398.8	47.2
0°-40°	632.6	74.8
0°-60°	837.7	99.0
0°-90°	845.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	526	
5°	522	50
15°	498	141
25°	454	209
35°	380	234
45°	203	157
55°	49	48
65°	6	7
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641826

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693BB - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	525.8
2.5°	524.7
5°	522.5
7.5°	519.3
10°	513.8
12.5°	506.2
15°	498.5
17.5°	489.8
20°	478.9
22.5°	466.9
25°	453.8
27.5°	438.5
30°	421.1
32.5°	402.5
35°	379.6
37.5°	349.1
40°	310.9
42.5°	260.7
45°	202.9
47.5°	150.5
50°	106.9
52.5°	73.1
55°	49.1
57.5°	31.6
60°	19.6
62.5°	10.9
65°	5.5
67.5°	2.2
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)