

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641867

Luminaire Tested: ML5612LSVWFL97FS1E - 693WB - 600LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-109)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 693WB - 600LM - 3000K
Description: ML56 RR, MILKY OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 874.7 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.22
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641867
CATALOG NUMBER: ML5612LSVWFL97FS1E - 693WB - 600LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641867

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693WB - 600LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	79																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70																			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62																			
5	83	73	65	59	81	71	64	59	70	63	58	68	62	58	66	61	57	56																			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	48	43	39	38																			
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26385
5°	26337
10°	26157
15°	25823
20°	25471
25°	25036
30°	24371
35°	23423
40°	20975
45°	16009
50°	10746
55°	7359
60°	5471
65°	4540
70°	4215
75°	4257
80°	4136
85°	3837

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16009 cd/sqm



TEST NUMBER: P641867

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693WB - 600LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	5.2
10°-20°	128.4	14.7
20°-30°	190.3	21.8
30°-40°	215.9	24.7
40°-50°	159.0	18.2
50°-60°	72.1	8.2
60°-70°	35.6	4.1
70°-80°	20.9	2.4
80°-90°	7.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.1	41.6
0°-40°	580.1	66.3
0°-60°	811.2	92.7
0°-90°	874.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	874.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	481	
5°	479	45
15°	455	128
25°	414	190
35°	350	216
45°	206	159
55°	77	72
65°	35	36
75°	20	21
85°	6	7
90°	0	



TEST NUMBER: P641867

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693WB - 600LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	481.3
2.5°	481.3
5°	478.6
7.5°	475.1
10°	469.9
12.5°	462.9
15°	455.0
17.5°	447.1
20°	436.6
22.5°	426.1
25°	413.9
27.5°	399.9
30°	385.0
32.5°	368.4
35°	350.0
37.5°	324.6
40°	293.1
42.5°	252.0
45°	206.5
47.5°	162.8
50°	126.0
52.5°	98.0
55°	77.0
57.5°	61.3
60°	49.9
62.5°	41.1
65°	35.0
67.5°	29.8
70°	26.3
72.5°	22.8
75°	20.1
77.5°	16.6
80°	13.1
82.5°	10.5
85°	6.1
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)