

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641869

Luminaire Tested: ML5612LSVWFL97FS1E - 693WB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-109)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 693WB - 600LM - 4000K
Description: ML56 RR, MILKY OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 966.8 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.22
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641869
CATALOG NUMBER: ML5612LSVWFL97FS1E - 693WB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641869

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693WB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	79																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70																			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62																			
5	83	73	65	59	81	71	64	59	70	63	58	68	62	58	66	61	57	56																			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	48	43	39	38																			
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29159
5°	29111
10°	28913
15°	28542
20°	28154
25°	27673
30°	26935
35°	25893
40°	23186
45°	17692
50°	11880
55°	8134
60°	6041
65°	5020
70°	4648
75°	4702
80°	4578
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17692 cd/sqm



TEST NUMBER: P641869

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693WB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	5.2
10°-20°	141.9	14.7
20°-30°	210.4	21.8
30°-40°	238.7	24.7
40°-50°	175.8	18.2
50°-60°	79.6	8.2
60°-70°	39.3	4.1
70°-80°	23.1	2.4
80°-90°	7.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	402.5	41.6
0°-40°	641.2	66.3
0°-60°	896.6	92.7
0°-90°	966.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	966.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	532	
5°	529	50
15°	503	142
25°	458	210
35°	387	239
45°	228	176
55°	85	80
65°	39	39
75°	22	23
85°	7	8
90°	0	



TEST NUMBER: P641869

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693WB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	531.9
2.5°	531.9
5°	529.0
7.5°	525.2
10°	519.4
12.5°	511.6
15°	502.9
17.5°	494.2
20°	482.6
22.5°	471.0
25°	457.5
27.5°	442.0
30°	425.5
32.5°	407.2
35°	386.9
37.5°	358.8
40°	324.0
42.5°	278.5
45°	228.2
47.5°	179.9
50°	139.3
52.5°	108.3
55°	85.1
57.5°	67.7
60°	55.1
62.5°	45.5
65°	38.7
67.5°	32.9
70°	29.0
72.5°	25.1
75°	22.2
77.5°	18.4
80°	14.5
82.5°	11.6
85°	6.8
87.5°	2.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)