

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641413

Luminaire Tested: ML5612LSVWFL7597FS1E - 691WB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-82)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 691WB - 1200LM - 3500K
Description: ML56 RR, 75D TIR OPTIC, 6" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1525.3 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641413

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 691WB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P641413

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 691WB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92																			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	85	79	74	92	84	78	73	82	76	72	79	75	72	78	74	71	69																			
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63																			
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58																			
7	78	67	61	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53																			
8	73	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	50	49																			
9	69	58	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45																			
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56158
5°	56983
10°	58889
15°	61226
20°	61880
25°	58582
30°	52654
35°	42590
40°	29563
45°	17746
50°	11309
55°	7073
60°	4747
65°	3074
70°	1571
75°	890
80°	884
85°	881

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17746 cd/sqm



TEST NUMBER: P641413

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 691WB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	6.5
10°-20°	303.8	19.9
20°-30°	441.7	29.0
30°-40°	391.1	25.6
40°-50°	188.0	12.3
50°-60°	70.0	4.6
60°-70°	24.0	1.6
70°-80°	5.3	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	845.0	55.4
0°-40°	1236.1	81.0
0°-60°	1494.0	97.9
0°-90°	1525.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1525.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1024	
5°	1036	100
15°	1079	304
25°	968	442
35°	636	391
45°	229	188
55°	74	70
65°	24	24
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P641413

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 691WB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1024.4
2.5°	1027.2
5°	1035.5
7.5°	1046.7
10°	1057.9
12.5°	1069.0
15°	1078.8
17.5°	1077.4
20°	1060.7
22.5°	1021.6
25°	968.5
27.5°	907.1
30°	831.8
32.5°	741.1
35°	636.4
37.5°	523.3
40°	413.1
42.5°	311.2
45°	228.9
47.5°	173.1
50°	132.6
52.5°	97.7
55°	74.0
57.5°	55.8
60°	43.3
62.5°	33.5
65°	23.7
67.5°	14.0
70°	9.8
72.5°	5.6
75°	4.2
77.5°	4.2
80°	2.8
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)