

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641891

Luminaire Tested: ML5612LSVWFL97FS1E - 694WB - 1200LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641891  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-113)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 694WB - 1200LM - 2700K  
Description: ML56 RR, MILKY OPTIC, 6" WHITE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1434.4 lumens  
Efficiency: N/A  
Efficacy: 86.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641891  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 694WB - 1200LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641891

CATALOG NUMBER: ML5612LSVWFL97FS1E - 694WB - 1200LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	94	88	83	99	92	86	82	88	84	80	85	81	78	82	79	76	74																			
3	93	83	76	70	91	82	75	70	79	73	68	76	71	67	74	70	66	64																			
4	86	75	67	61	84	73	66	60	71	64	59	69	63	59	67	62	58	56																			
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	61	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	51	46	55	50	45	43																			
7	68	56	47	42	67	55	47	41	53	46	41	52	46	41	51	45	41	39																			
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35																			
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	38	33	32																			
10	56	44	36	31	55	43	36	31	42	35	31	41	35	31	40	35	30	29																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34548
5°	34537
10°	34491
15°	34268
20°	33912
25°	33407
30°	32530
35°	31126
40°	29312
45°	27042
50°	24229
55°	21342
60°	18102
65°	15255
70°	12919
75°	11184
80°	10008
85°	10001

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27042 cd/sqm



TEST NUMBER: P641891

CATALOG NUMBER: ML5612LSVWFL97FS1E - 694WB - 1200LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.7	4.2
10°-20°	170.2	11.9
20°-30°	253.9	17.7
30°-40°	290.2	20.2
40°-50°	268.2	18.7
50°-60°	199.6	13.9
60°-70°	118.1	8.2
70°-80°	57.3	4.0
80°-90°	17.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.7	33.7
0°-40°	773.9	54.0
0°-60°	1241.7	86.6
0°-90°	1434.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1434.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	630	
5°	628	60
15°	604	170
25°	552	254
35°	465	290
45°	349	268
55°	223	200
65°	118	118
75°	53	57
85°	16	17
90°	0	



TEST NUMBER: P641891

CATALOG NUMBER: ML5612LSVWFL97FS1E - 694WB - 1200LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	630.2
2.5°	630.2
5°	627.6
7.5°	624.9
10°	619.6
12.5°	611.7
15°	603.8
17.5°	593.2
20°	581.3
22.5°	568.1
25°	552.3
27.5°	533.8
30°	513.9
32.5°	490.2
35°	465.1
37.5°	438.6
40°	409.6
42.5°	379.2
45°	348.8
47.5°	317.1
50°	284.1
52.5°	253.7
55°	223.3
57.5°	192.9
60°	165.1
62.5°	140.0
65°	117.6
67.5°	97.8
70°	80.6
72.5°	66.1
75°	52.8
77.5°	42.3
80°	31.7
82.5°	22.5
85°	15.9
87.5°	9.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)