

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641434

Luminaire Tested: ML5612LSVWFL7597FS1E - 692H - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641434
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-84)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 692H - 600LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 6" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1048.9 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.08
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641434
CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692H - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641434

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692H - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																											
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																											
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77																											
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70																											
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65																											
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59																											
7	79	69	62	57	77	68	62	57	67	61	57	65	60	56	64	60	56	55																											
8	74	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50																											
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47																											
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	367518
5°	373231
10°	383358
15°	396266
20°	397195
25°	374482
30°	333563
35°	268809
40°	184781
45°	107173
50°	59333
55°	35698
60°	19044
65°	5604
70°	1443
75°	1906
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 107173 cd/sqm



TEST NUMBER: P641434

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692H - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	6.9
10°-20°	218.2	20.8
20°-30°	313.1	29.9
30°-40°	274.2	26.1
40°-50°	125.3	11.9
50°-60°	38.9	3.7
60°-70°	6.2	0.6
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.6	57.5
0°-40°	877.8	83.7
0°-60°	1042.0	99.3
0°-90°	1048.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1048.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	745	
5°	754	72
15°	776	218
25°	688	313
35°	446	274
45°	154	125
55°	42	39
65°	5	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641434

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692H - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	744.9
2.5°	747.8
5°	753.6
7.5°	759.4
10°	765.2
12.5°	771.9
15°	775.8
17.5°	771.9
20°	756.5
22.5°	726.5
25°	687.9
27.5°	640.5
30°	585.5
32.5°	520.7
35°	446.3
37.5°	366.2
40°	286.9
42.5°	212.5
45°	153.6
47.5°	110.1
50°	77.3
52.5°	56.0
55°	41.5
57.5°	29.9
60°	19.3
62.5°	8.7
65°	4.8
67.5°	1.9
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)