

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641917

Luminaire Tested: ML5612LSVWFL97FS1E - 696WB - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641917  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-115)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 696WB - 900LM - 3000K  
Description: ML56 RR, MILKY OPTIC, 6" SHALLOW WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1165.9 lumens  
Efficiency: N/A  
Efficacy: 87.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.28  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641917

CATALOG NUMBER: ML5612LSVWFL97FS1E - 696WB - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641917

CATALOG NUMBER: ML5612LSVWFL97FS1E - 696WB - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	101	95	89	85	91	87	83	88	84	81	85	82	80	78			
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	88	78	71	65	86	77	70	64	75	68	64	72	67	63	70	66	62	60			
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	53			
6	76	64	57	51	75	64	56	51	62	55	50	60	54	50	59	54	49	48			
7	71	59	51	46	69	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	66	54	46	41	65	54	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	31598
5°	31532
10°	31396
15°	31186
20°	30809
25°	30316
30°	29530
35°	28442
40°	26879
45°	24514
50°	20085
55°	14470
60°	9955
65°	6836
70°	4857
75°	3791
80°	3883
85°	4214

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24514 cd/sqm



TEST NUMBER: P641917

CATALOG NUMBER: ML5612LSVWFL97FS1E - 696WB - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.4	4.7
10°-20°	154.8	13.3
20°-30°	230.4	19.8
30°-40°	264.7	22.7
40°-50°	240.3	20.6
50°-60°	138.7	11.9
60°-70°	55.0	4.7
70°-80°	20.7	1.8
80°-90°	6.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.7	37.7
0°-40°	704.4	60.4
0°-60°	1083.4	92.9
0°-90°	1165.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1165.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	576	
5°	573	54
15°	550	155
25°	501	230
35°	425	265
45°	316	240
55°	151	139
65°	53	55
75°	18	21
85°	7	7
90°	0	



TEST NUMBER: P641917

CATALOG NUMBER: ML5612LSVWFL97FS1E - 696WB - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	576.4
2.5°	575.2
5°	573.0
7.5°	569.6
10°	564.0
12.5°	557.3
15°	549.5
17.5°	539.4
20°	528.1
22.5°	515.8
25°	501.2
27.5°	484.4
30°	466.5
32.5°	446.3
35°	425.0
37.5°	400.3
40°	375.6
42.5°	347.6
45°	316.2
47.5°	279.2
50°	235.5
52.5°	191.7
55°	151.4
57.5°	117.7
60°	90.8
62.5°	69.5
65°	52.7
67.5°	40.4
70°	30.3
72.5°	23.5
75°	17.9
77.5°	15.7
80°	12.3
82.5°	10.1
85°	6.7
87.5°	2.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)