

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641458

Luminaire Tested: ML5612LSVWFL7597FS1E - 692W - 1200LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641458  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-85)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL7597FS1E - 692W - 1200LM - 3500K  
Description: ML56 RR, 75D TIR OPTIC, 6" WHITE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1526.7 lumens  
Efficiency: N/A  
Efficacy: 92.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641458

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692W - 1200LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P641458

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692W - 1200LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	57643
5°	58557
10°	60320
15°	62532
20°	63215
25°	59804
30°	53565
35°	43085
40°	29577
45°	17320
50°	10004
55°	6404
60°	3826
65°	1816
70°	1122
75°	1186
80°	884
85°	881

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17320 cd/sqm



TEST NUMBER: P641458

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692W - 1200LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.2	6.7
10°-20°	310.5	20.3
20°-30°	450.8	29.5
30°-40°	395.3	25.9
40°-50°	182.6	12.0
50°-60°	62.1	4.1
60°-70°	15.8	1.0
70°-80°	5.7	0.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	863.6	56.6
0°-40°	1258.9	82.5
0°-60°	1503.6	98.5
0°-90°	1526.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1526.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1052	
5°	1064	102
15°	1102	311
25°	989	451
35°	644	395
45°	223	183
55°	67	62
65°	14	16
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P641458

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692W - 1200LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1051.5
2.5°	1055.7
5°	1064.1
7.5°	1075.2
10°	1083.6
12.5°	1094.8
15°	1101.8
17.5°	1100.4
20°	1083.6
22.5°	1044.5
25°	988.7
27.5°	925.8
30°	846.2
32.5°	751.3
35°	643.8
37.5°	526.5
40°	413.3
42.5°	308.6
45°	223.4
47.5°	162.0
50°	117.3
52.5°	86.6
55°	67.0
57.5°	50.3
60°	34.9
62.5°	20.9
65°	14.0
67.5°	8.4
70°	7.0
72.5°	7.0
75°	5.6
77.5°	4.2
80°	2.8
82.5°	2.8
85°	1.4
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)