

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641959

Luminaire Tested: ML5612LSWFL5597FS1E - 592SC - 600LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641959  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-48)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSWFL5597FS1E - 592SC - 600LM - 4000K  
Description: ML56 RR, 55D TIR OPTIC, 5" SPECULAR CLEAR TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1089.5 lumens  
Efficiency: N/A  
Efficacy: 105.8 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.88  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641959

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592SC - 600LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641959

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592SC - 600LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80																			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74																			
5	91	82	76	72	89	82	76	72	80	75	71	78	74	70	76	73	70	68																			
6	86	77	71	66	85	76	70	66	75	70	66	73	69	65	72	68	65	63																			
7	82	72	66	62	80	71	66	61	70	65	61	69	64	61	68	64	60	59																			
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55																			
9	74	64	58	53	73	63	57	53	62	57	53	61	56	53	60	56	53	51																			
10	70	60	54	50	69	60	54	50	59	54	50	58	53	50	57	53	50	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	95424
5°	91351
10°	86283
15°	82036
20°	73195
25°	61067
30°	49451
35°	38393
40°	27803
45°	16846
50°	5588
55°	2532
60°	758
65°	187
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16846 cd/sqm



TEST NUMBER: P641959

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592SC - 600LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.6	9.9
10°-20°	278.1	25.5
20°-30°	321.3	29.5
30°-40°	248.7	22.8
40°-50°	114.3	10.5
50°-60°	18.1	1.7
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	707.1	64.9
0°-40°	955.8	87.7
0°-60°	1088.2	99.9
0°-90°	1089.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1089.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1209	
5°	1153	108
15°	1004	278
25°	701	321
35°	398	249
45°	151	114
55°	18	18
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641959  
CATALOG NUMBER: ML5612LSWFL5597FS1E - 592SC - 600LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1208.8
2.5°	1192.4
5°	1152.8
7.5°	1111.2
10°	1076.4
12.5°	1044.4
15°	1003.8
17.5°	943.9
20°	871.3
22.5°	790.1
25°	701.1
27.5°	618.0
30°	542.5
32.5°	470.0
35°	398.4
37.5°	330.7
40°	269.8
42.5°	211.8
45°	150.9
47.5°	83.2
50°	45.5
52.5°	28.0
55°	18.4
57.5°	10.6
60°	4.8
62.5°	1.9
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)