

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641481

Luminaire Tested: ML5612LSVWFL7597FS1E - 693BB - 900LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641481  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-87)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL7597FS1E - 693BB - 900LM - 2700K  
Description: ML56 RR, 75D TIR OPTIC, 6" BLACK BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1146.6 lumens  
Efficiency: N/A  
Efficacy: 86.2 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641481

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693BB - 900LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641481

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693BB - 900LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92																
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77																
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71			71																
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	73	69	66	65			65																
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59																
7	79	69	62	57	78	68	62	57	67	61	57	65	60	56	64	60	56	55			55																
8	75	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50			50																
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47			47																
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43			43																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	43971
5°	44679
10°	46102
15°	47872
20°	48380
25°	45874
30°	41032
35°	32933
40°	22413
45°	12947
50°	7070
55°	4272
60°	2149
65°	571
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12947 cd/sqm



TEST NUMBER: P641481

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693BB - 900LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	6.8
10°-20°	237.6	20.7
20°-30°	345.4	30.1
30°-40°	301.8	26.3
40°-50°	136.1	11.9
50°-60°	41.5	3.6
60°-70°	6.1	0.5
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	661.1	57.7
0°-40°	962.9	84.0
0°-60°	1140.5	99.5
0°-90°	1146.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1146.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	802	
5°	812	78
15°	844	238
25°	758	345
35°	492	302
45°	167	136
55°	45	42
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641481

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693BB - 900LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	802.1
2.5°	805.3
5°	811.9
7.5°	820.6
10°	828.2
12.5°	837.0
15°	843.5
17.5°	842.4
20°	829.3
22.5°	799.9
25°	758.4
27.5°	709.3
30°	648.2
32.5°	574.0
35°	492.1
37.5°	401.6
40°	313.2
42.5°	232.4
45°	167.0
47.5°	117.9
50°	82.9
52.5°	60.0
55°	44.7
57.5°	31.6
60°	19.6
62.5°	9.8
65°	4.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)