

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641977

Luminaire Tested: ML5612LSWFL5597FS1E - 592W - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-50)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 592W - 900LM - 3000K
Description: ML56 RR, 55D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1259.1 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641977
CATALOG NUMBER: ML5612LSWFL5597FS1E - 592W - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641977

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592W - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																												
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																												
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79																												
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	72																												
5	90	81	75	71	89	81	75	70	79	74	70	77	73	69	75	72	68	67																												
6	85	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62																												
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58																												
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54																												
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50																												
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105686
5°	101288
10°	96078
15°	90429
20°	81831
25°	69699
30°	56880
35°	44445
40°	32378
45°	20050
50°	7307
55°	3867
60°	1942
65°	1476
70°	1546
75°	1373
80°	1546
85°	996

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20050 cd/sqm



TEST NUMBER: P641977

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592W - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.5	9.5
10°-20°	308.1	24.5
20°-30°	365.4	29.0
30°-40°	287.7	22.8
40°-50°	135.5	10.8
50°-60°	27.6	2.2
60°-70°	8.4	0.7
70°-80°	5.2	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	793.1	63.0
0°-40°	1080.8	85.8
0°-60°	1243.8	98.8
0°-90°	1259.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1259.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1339	
5°	1278	120
15°	1106	308
25°	800	365
35°	461	288
45°	180	135
55°	28	28
65°	8	8
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P641977

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592W - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1338.8
2.5°	1322.0
5°	1278.2
7.5°	1235.6
10°	1198.6
12.5°	1155.9
15°	1106.5
17.5°	1044.8
20°	974.1
22.5°	891.1
25°	800.2
27.5°	709.3
30°	624.0
32.5°	542.0
35°	461.2
37.5°	383.8
40°	314.2
42.5°	246.9
45°	179.6
47.5°	101.0
50°	59.5
52.5°	40.4
55°	28.1
57.5°	20.2
60°	12.3
62.5°	10.1
65°	7.9
67.5°	6.7
70°	6.7
72.5°	5.6
75°	4.5
77.5°	4.5
80°	3.4
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)