

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641574

Luminaire Tested: ML5612LSVWFL7597FS1E - 696WB - 900LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641574  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-92)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL7597FS1E - 696WB - 900LM - 4000K  
Description: ML56 RR, 75D TIR OPTIC, 6" SHALLOW WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1360.6 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641574

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 696WB - 900LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641574

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 696WB - 900LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	99	98	96	96	95	94	92																			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76																			
4	94	85	79	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69																			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63																			
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58																			
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	55	53																			
8	73	63	56	51	72	62	56	51	61	55	51	60	54	51	59	54	50	49																			
9	69	58	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45																			
10	66	55	48	44	64	54	48	44	53	48	44	52	47	43	52	47	43	42																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	50155
5°	50688
10°	52376
15°	54455
20°	55106
25°	52261
30°	46767
35°	37912
40°	26349
45°	15955
50°	10149
55°	6518
60°	4353
65°	2893
70°	1394
75°	784
80°	789
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15955 cd/sqm



TEST NUMBER: P641574

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 696WB - 900LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.6	6.5
10°-20°	270.4	19.9
20°-30°	393.1	28.9
30°-40°	348.1	25.6
40°-50°	168.1	12.4
50°-60°	64.1	4.7
60°-70°	22.1	1.6
70°-80°	4.4	0.3
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	752.1	55.3
0°-40°	1100.2	80.9
0°-60°	1332.4	97.9
0°-90°	1360.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1360.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	915	
5°	921	89
15°	960	270
25°	864	393
35°	566	348
45°	206	168
55°	68	64
65°	22	22
75°	4	4
85°	1	2
90°	0	



TEST NUMBER: P641574

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 696WB - 900LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	914.9
2.5°	918.6
5°	921.1
7.5°	931.0
10°	940.9
12.5°	952.0
15°	959.5
17.5°	959.5
20°	944.6
22.5°	909.9
25°	864.0
27.5°	805.8
30°	738.8
32.5°	659.5
35°	566.5
37.5°	466.1
40°	368.2
42.5°	278.9
45°	205.8
47.5°	153.7
50°	119.0
52.5°	90.5
55°	68.2
57.5°	50.8
60°	39.7
62.5°	29.8
65°	22.3
67.5°	13.6
70°	8.7
72.5°	5.0
75°	3.7
77.5°	2.5
80°	2.5
82.5°	2.5
85°	1.2
87.5°	1.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)