

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641576

Luminaire Tested: ML5612LSVWFL97FS1E - 591WB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-93)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 591WB - 1200LM - 2700K
Description: ML56 RR, MILKY OPTIC, 5" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1348.5 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641576
CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641576

CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68																			
4	89	78	71	65	87	77	70	65	75	69	64	73	67	63	71	66	62	61																			
5	82	71	64	58	81	70	63	58	68	62	57	66	61	56	65	60	56	54																			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49																			
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	44	39	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55961
5°	55858
10°	55550
15°	55124
20°	54445
25°	53463
30°	52103
35°	49611
40°	44487
45°	35512
50°	26097
55°	19075
60°	14588
65°	12085
70°	10963
75°	10858
80°	11411
85°	11956

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35512 cd/sqm



TEST NUMBER: P641576

CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.9	5.0
10°-20°	190.0	14.1
20°-30°	282.5	20.9
30°-40°	318.6	23.6
40°-50°	245.0	18.2
50°-60°	127.6	9.5
60°-70°	65.9	4.9
70°-80°	37.8	2.8
80°-90°	14.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.3	40.0
0°-40°	858.0	63.6
0°-60°	1230.6	91.3
0°-90°	1348.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1348.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	709	
5°	705	67
15°	674	190
25°	614	282
35°	515	319
45°	318	245
55°	139	128
65°	65	66
75°	36	38
85°	13	14
90°	0	



TEST NUMBER: P641576
CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	708.9
2.5°	707.5
5°	704.9
7.5°	699.6
10°	693.0
12.5°	683.8
15°	674.5
17.5°	661.3
20°	648.1
22.5°	632.3
25°	613.8
27.5°	594.0
30°	571.6
32.5°	545.2
35°	514.8
37.5°	477.9
40°	431.7
42.5°	377.5
45°	318.1
47.5°	260.0
50°	212.5
52.5°	170.3
55°	138.6
57.5°	112.2
60°	92.4
62.5°	76.6
65°	64.7
67.5°	55.4
70°	47.5
72.5°	40.9
75°	35.6
77.5°	30.4
80°	25.1
82.5°	19.8
85°	13.2
87.5°	6.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)