

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641580

Luminaire Tested: ML5612LSVWFL97FS1E - 591WB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-93)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 591WB - 1200LM - 5000K
Description: ML56 RR, MILKY OPTIC, 5" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1533.5 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641580
CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641580

CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68																			
4	89	78	71	65	87	77	70	65	75	69	64	73	67	63	71	66	62	61																			
5	82	71	64	58	81	70	63	58	68	62	57	66	61	56	65	60	56	54																			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49																			
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	44	39	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63642
5°	63529
10°	63173
15°	62692
20°	61922
25°	60806
30°	59250
35°	56424
40°	50587
45°	40391
50°	29683
55°	21690
60°	16593
65°	13748
70°	12464
75°	12353
80°	12956
85°	13586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 40391 cd/sqm



TEST NUMBER: P641580

CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.1	5.0
10°-20°	216.1	14.1
20°-30°	321.2	20.9
30°-40°	362.3	23.6
40°-50°	278.6	18.2
50°-60°	145.1	9.5
60°-70°	75.0	4.9
70°-80°	42.9	2.8
80°-90°	16.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.4	40.0
0°-40°	975.7	63.6
0°-60°	1399.5	91.3
0°-90°	1533.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1533.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	806	
5°	802	76
15°	767	216
25°	698	321
35°	586	362
45°	362	279
55°	158	145
65°	74	75
75°	40	43
85°	15	16
90°	0	



TEST NUMBER: P641580

CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	806.2
2.5°	804.7
5°	801.7
7.5°	795.6
10°	788.1
12.5°	777.6
15°	767.1
17.5°	752.1
20°	737.1
22.5°	719.1
25°	698.1
27.5°	675.5
30°	650.0
32.5°	620.0
35°	585.5
37.5°	543.4
40°	490.9
42.5°	429.3
45°	361.8
47.5°	295.7
50°	241.7
52.5°	193.7
55°	157.6
57.5°	127.6
60°	105.1
62.5°	87.1
65°	73.6
67.5°	63.1
70°	54.0
72.5°	46.5
75°	40.5
77.5°	34.5
80°	28.5
82.5°	22.5
85°	15.0
87.5°	7.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)