

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642061

Luminaire Tested: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 967.0 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642061

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642061

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92																
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61			61																
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57																
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53			53																
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49			49																
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79501
5°	76097
10°	72207
15°	68265
20°	61804
25°	52305
30°	42414
35°	32949
40°	24279
45°	15953
50°	7725
55°	4101
60°	2684
65°	2223
70°	1777
75°	1312
80°	773
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15953 cd/sqm



TEST NUMBER: P642061

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.8	9.3
10°-20°	232.5	24.0
20°-30°	274.4	28.4
30°-40°	213.9	22.1
40°-50°	109.4	11.3
50°-60°	29.8	3.1
60°-70°	12.1	1.3
70°-80°	4.6	0.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.8	61.7
0°-40°	810.7	83.8
0°-60°	949.8	98.2
0°-90°	967.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	967.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1007	
5°	960	90
15°	835	233
25°	600	274
35°	342	214
45°	143	109
55°	30	30
65°	12	12
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P642061

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1007.1
2.5°	994.3
5°	960.3
7.5°	928.8
10°	900.8
12.5°	871.0
15°	835.3
17.5°	790.2
20°	735.7
22.5°	671.9
25°	600.5
27.5°	530.8
30°	465.3
32.5°	401.5
35°	341.9
37.5°	285.8
40°	235.6
42.5°	188.0
45°	142.9
47.5°	94.4
50°	62.9
52.5°	42.5
55°	29.8
57.5°	22.1
60°	17.0
62.5°	14.5
65°	11.9
67.5°	10.2
70°	7.7
72.5°	6.0
75°	4.3
77.5°	2.6
80°	1.7
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)