

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642064

Luminaire Tested: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642064
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 4000K
Description: ML56 RR, 55D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1099.1 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642064

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642064

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92															
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61				61															
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				57															
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53				53															
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49				49															
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90379
5°	86509
10°	82083
15°	77599
20°	70264
25°	59464
30°	48211
35°	37459
40°	27597
45°	18130
50°	8793
55°	4652
60°	3047
65°	2522
70°	2008
75°	1464
80°	864
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18130 cd/sqm



TEST NUMBER: P642064

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	9.3
10°-20°	264.4	24.1
20°-30°	312.0	28.4
30°-40°	243.1	22.1
40°-50°	124.3	11.3
50°-60°	33.8	3.1
60°-70°	13.7	1.2
70°-80°	5.2	0.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.5	61.7
0°-40°	921.6	83.8
0°-60°	1079.7	98.2
0°-90°	1099.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1099.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1145	
5°	1092	102
15°	950	264
25°	683	312
35°	389	243
45°	162	124
55°	34	34
65°	14	14
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P642064

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1144.9
2.5°	1130.4
5°	1091.7
7.5°	1055.9
10°	1024.0
12.5°	990.2
15°	949.5
17.5°	898.3
20°	836.4
22.5°	763.9
25°	682.7
27.5°	603.4
30°	528.9
32.5°	456.4
35°	388.7
37.5°	324.9
40°	267.8
42.5°	213.7
45°	162.4
47.5°	107.3
50°	71.6
52.5°	48.3
55°	33.8
57.5°	25.1
60°	19.3
62.5°	16.4
65°	13.5
67.5°	11.6
70°	8.7
72.5°	6.8
75°	4.8
77.5°	2.9
80°	1.9
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)