

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641589

Luminaire Tested: ML5612LSVWFL97FS1E - 591WB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-93)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 591WB - 900LM - 4000K
Description: ML56 RR, MILKY OPTIC, 5" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1266.4 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641589
CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641589

CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68																			
4	89	78	71	65	87	77	70	65	75	69	64	73	67	63	71	66	62	61																			
5	82	71	64	58	81	70	63	58	68	62	57	66	61	56	65	60	56	54																			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49																			
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	44	39	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52551
5°	52459
10°	52167
15°	51773
20°	51135
25°	50205
30°	48931
35°	46594
40°	41776
45°	33358
50°	24513
55°	17919
60°	13704
65°	11338
70°	10294
75°	10218
80°	10729
85°	11231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33358 cd/sqm



TEST NUMBER: P641589

CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.8	5.0
10°-20°	178.4	14.1
20°-30°	265.3	20.9
30°-40°	299.2	23.6
40°-50°	230.1	18.2
50°-60°	119.9	9.5
60°-70°	61.9	4.9
70°-80°	35.5	2.8
80°-90°	13.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	506.5	40.0
0°-40°	805.7	63.6
0°-60°	1155.7	91.3
0°-90°	1266.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1266.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	662	63
15°	634	178
25°	576	265
35°	484	299
45°	299	230
55°	130	120
65°	61	62
75°	34	35
85°	12	13
90°	0	



TEST NUMBER: P641589

CATALOG NUMBER: ML5612LSVWFL97FS1E - 591WB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	665.7
2.5°	664.4
5°	662.0
7.5°	657.0
10°	650.8
12.5°	642.1
15°	633.5
17.5°	621.1
20°	608.7
22.5°	593.8
25°	576.4
27.5°	557.8
30°	536.8
32.5°	512.0
35°	483.5
37.5°	448.7
40°	405.4
42.5°	354.5
45°	298.8
47.5°	244.2
50°	199.6
52.5°	159.9
55°	130.2
57.5°	105.4
60°	86.8
62.5°	71.9
65°	60.7
67.5°	52.1
70°	44.6
72.5°	38.4
75°	33.5
77.5°	28.5
80°	23.6
82.5°	18.6
85°	12.4
87.5°	6.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)