

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641595

Luminaire Tested: ML5612LSVWFL97FS1E - 592H - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-95)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592H - 1200LM - 5000K
Description: ML56 RR, MILKY OPTIC, 5" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1472.6 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.97
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641595
CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641595

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77																
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71			71																
5	89	80	73	68	87	79	73	68	77	72	68	75	71	67	74	70	66	65			65																
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	64	61	60			60																
7	79	69	62	58	78	68	62	57	67	61	57	66	61	57	64	60	56	55			55																
8	75	64	58	53	73	64	57	53	63	57	53	61	56	53	60	56	52	51			51																
9	71	60	54	49	70	60	53	49	59	53	49	58	53	49	57	52	49	47			47																
10	67	56	50	46	66	56	50	46	55	50	46	54	49	46	54	49	45	44			44																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108489
5°	106169
10°	99934
15°	91696
20°	83780
25°	76406
30°	68593
35°	58043
40°	42415
45°	26492
50°	15130
55°	8272
60°	4263
65°	1961
70°	1039
75°	458
80°	682
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26492 cd/sqm



TEST NUMBER: P641595

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.9	8.5
10°-20°	314.4	21.4
20°-30°	402.3	27.3
30°-40°	368.9	25.0
40°-50°	189.7	12.9
50°-60°	57.8	3.9
60°-70°	12.0	0.8
70°-80°	2.4	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	841.6	57.2
0°-40°	1210.5	82.2
0°-60°	1458.0	99.0
0°-90°	1472.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1472.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1374	
5°	1340	125
15°	1122	314
25°	877	402
35°	602	369
45°	237	190
55°	60	58
65°	10	12
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P641595

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1374.3
2.5°	1365.3
5°	1339.8
7.5°	1299.2
10°	1246.7
12.5°	1185.1
15°	1122.0
17.5°	1058.9
20°	997.3
22.5°	937.3
25°	877.2
27.5°	815.6
30°	752.5
32.5°	681.9
35°	602.3
37.5°	509.2
40°	411.6
42.5°	318.4
45°	237.3
47.5°	172.7
50°	123.2
52.5°	85.6
55°	60.1
57.5°	40.6
60°	27.0
62.5°	16.5
65°	10.5
67.5°	6.0
70°	4.5
72.5°	3.0
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)