

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642092

Luminaire Tested: ML5612LSWFL5597FS1E - 596WB - 600LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-58)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 596WB - 600LM - 3000K
Description: ML56 RR, 55D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1005.8 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642092
CATALOG NUMBER: ML5612LSWFL5597FS1E - 596WB - 600LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642092

CATALOG NUMBER: ML5612LSWFL5597FS1E - 596WB - 600LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			85																
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	81	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	63	61			61																
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57																
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53			53																
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49			49																
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82170
5°	78601
10°	74676
15°	70554
20°	63854
25°	54090
30°	44091
35°	34645
40°	26051
45°	17382
50°	8376
55°	3730
60°	2352
65°	1625
70°	1200
75°	793
80°	1591
85°	2355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17382 cd/sqm



TEST NUMBER: P642092

CATALOG NUMBER: ML5612LSWFL5597FS1E - 596WB - 600LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.8	9.2
10°-20°	240.3	23.9
20°-30°	283.8	28.2
30°-40°	225.2	22.4
40°-50°	118.7	11.8
50°-60°	28.9	2.9
60°-70°	9.2	0.9
70°-80°	4.2	0.4
80°-90°	2.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	617.0	61.3
0°-40°	842.1	83.7
0°-60°	989.7	98.4
0°-90°	1005.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1005.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1041	
5°	992	93
15°	863	240
25°	621	284
35°	360	225
45°	156	119
55°	27	29
65°	9	9
75°	3	4
85°	3	3
90°	0	



TEST NUMBER: P642092

CATALOG NUMBER: ML5612LSWFL5597FS1E - 596WB - 600LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1040.9
2.5°	1026.9
5°	991.9
7.5°	959.5
10°	931.6
12.5°	900.1
15°	863.3
17.5°	816.1
20°	760.1
22.5°	693.6
25°	621.0
27.5°	549.3
30°	483.7
32.5°	420.7
35°	359.5
37.5°	303.5
40°	252.8
42.5°	202.9
45°	155.7
47.5°	104.1
50°	68.2
52.5°	42.9
55°	27.1
57.5°	19.2
60°	14.9
62.5°	11.4
65°	8.7
67.5°	7.0
70°	5.2
72.5°	4.4
75°	2.6
77.5°	4.4
80°	3.5
82.5°	3.5
85°	2.6
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)