

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642093

Luminaire Tested: ML5612LSWFL5597FS1E - 596WB - 600LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642093  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-58)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSWFL5597FS1E - 596WB - 600LM - 3500K  
Description: ML56 RR, 55D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1033.3 lumens  
Efficiency: N/A  
Efficacy: 100.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642093

CATALOG NUMBER: ML5612LSWFL5597FS1E - 596WB - 600LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P642093

CATALOG NUMBER: ML5612LSWFL5597FS1E - 596WB - 600LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	81	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57	57	57	57
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53	53	53	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49	49	49	49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	84404
5°	80740
10°	76704
15°	72474
20°	65593
25°	55562
30°	45294
35°	35589
40°	26762
45°	17851
50°	8609
55°	3840
60°	2416
65°	1681
70°	1246
75°	824
80°	1637
85°	2446

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17851 cd/sqm



TEST NUMBER: P642093

CATALOG NUMBER: ML5612LSWFL5597FS1E - 596WB - 600LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.4	9.2
10°-20°	246.8	23.9
20°-30°	291.6	28.2
30°-40°	231.3	22.4
40°-50°	121.9	11.8
50°-60°	29.7	2.9
60°-70°	9.4	0.9
70°-80°	4.3	0.4
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	633.8	61.3
0°-40°	865.1	83.7
0°-60°	1016.7	98.4
0°-90°	1033.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1069	
5°	1019	95
15°	887	247
25°	638	292
35°	369	231
45°	160	122
55°	28	30
65°	9	9
75°	3	4
85°	3	3
90°	0	



TEST NUMBER: P642093

CATALOG NUMBER: ML5612LSWFL5597FS1E - 596WB - 600LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1069.2
2.5°	1054.9
5°	1018.9
7.5°	985.7
10°	956.9
12.5°	924.6
15°	886.8
17.5°	838.3
20°	780.8
22.5°	712.5
25°	637.9
27.5°	564.3
30°	496.9
32.5°	432.2
35°	369.3
37.5°	311.8
40°	259.7
42.5°	208.5
45°	159.9
47.5°	106.9
50°	70.1
52.5°	44.0
55°	27.9
57.5°	19.8
60°	15.3
62.5°	11.7
65°	9.0
67.5°	7.2
70°	5.4
72.5°	4.5
75°	2.7
77.5°	4.5
80°	3.6
82.5°	3.6
85°	2.7
87.5°	2.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)