

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641615

Luminaire Tested: ML5612LSVWFL97FS1E - 592SC - 600LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-94)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592SC - 600LM - 5000K
Description: ML56 RR, MILKY OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 977.7 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.95
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641615

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 600LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641615

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 600LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																											
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																											
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78																											
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71																											
5	90	81	74	69	88	80	74	69	78	73	69	76	71	68	74	70	67	66																											
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61																											
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	65	61	58	56																											
8	76	65	59	54	74	65	59	54	64	58	54	63	57	54	62	57	54	52																											
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48																											
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75120
5°	75708
10°	72864
15°	65045
20°	56864
25°	50118
30°	44246
35°	37555
40°	27700
45°	17170
50°	9260
55°	4652
60°	2131
65°	897
70°	439
75°	305
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17170 cd/sqm



TEST NUMBER: P641615

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 600LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	9.2
10°-20°	222.0	22.7
20°-30°	264.5	27.1
30°-40°	238.8	24.4
40°-50°	122.8	12.6
50°-60°	33.3	3.4
60°-70°	5.4	0.6
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	576.3	58.9
0°-40°	815.1	83.4
0°-60°	971.3	99.3
0°-90°	977.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	977.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	952	
5°	955	90
15°	796	222
25°	575	265
35°	390	239
45°	154	123
55°	34	33
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641615

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 600LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	951.6
2.5°	953.5
5°	955.4
7.5°	942.8
10°	909.0
12.5°	857.8
15°	795.9
17.5°	734.9
20°	676.9
22.5°	622.8
25°	575.4
27.5°	529.0
30°	485.4
32.5°	439.0
35°	389.7
37.5°	331.7
40°	268.8
42.5°	208.9
45°	153.8
47.5°	110.2
50°	75.4
52.5°	50.3
55°	33.8
57.5°	22.2
60°	13.5
62.5°	7.7
65°	4.8
67.5°	1.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)