

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642109

Luminaire Tested: ML5612LSWFL5597FS1E - 691WB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 691WB - 600LM - 4000K
Description: ML56 RR, 55D TIR OPTIC, 6" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1093.4 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642109
CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642109

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																											
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																											
3	101	94	89	84	99	93	88	84	90	86	82	88	84	81	85	82	80	78																											
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72																											
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66																											
6	85	76	69	65	84	75	69	64	73	68	64	72	67	63	70	66	63	61																											
7	81	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57																											
8	76	66	60	55	75	66	59	55	64	59	55	63	58	55	62	58	54	53																											
9	72	62	56	52	71	62	56	51	61	55	51	60	55	51	59	54	51	49																											
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62648
5°	60015
10°	56996
15°	53718
20°	48561
25°	41113
30°	33474
35°	26207
40°	19508
45°	13118
50°	6345
55°	3144
60°	1590
65°	999
70°	465
75°	402
80°	316
85°	629

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13118 cd/sqm



TEST NUMBER: P642109

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	9.3
10°-20°	263.5	24.1
20°-30°	310.5	28.4
30°-40°	245.0	22.4
40°-50°	128.6	11.8
50°-60°	32.9	3.0
60°-70°	7.8	0.7
70°-80°	2.0	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.1	61.8
0°-40°	921.1	84.2
0°-60°	1082.6	99.0
0°-90°	1093.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1093.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1143	
5°	1091	102
15°	946	264
25°	680	311
35°	392	245
45°	169	129
55°	33	33
65°	8	8
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P642109

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1142.8
2.5°	1128.3
5°	1090.6
7.5°	1054.8
10°	1023.9
12.5°	988.1
15°	946.5
17.5°	894.3
20°	832.4
22.5°	759.0
25°	679.7
27.5°	600.4
30°	528.8
32.5°	458.3
35°	391.6
37.5°	329.7
40°	272.6
42.5°	219.5
45°	169.2
47.5°	113.1
50°	74.4
52.5°	50.3
55°	32.9
57.5°	21.3
60°	14.5
62.5°	10.6
65°	7.7
67.5°	4.8
70°	2.9
72.5°	1.9
75°	1.9
77.5°	1.9
80°	1.0
82.5°	1.0
85°	1.0
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)