

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641628

Luminaire Tested: ML5612LSVWFL97FS1E - 592W - 600LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-96)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592W - 600LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 876.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641628

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 600LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P641628

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 600LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	62	58	66	61	58	56																			
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	54	48	59	53	48	58	52	48	57	52	48	46																			
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42																			
9	65	53	45	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28413
5°	28324
10°	28000
15°	27531
20°	26987
25°	26409
30°	25358
35°	22901
40°	18256
45°	12955
50°	9424
55°	7302
60°	6304
65°	5824
70°	5466
75°	5147
80°	4546
85°	3397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12955 cd/sqm



TEST NUMBER: P641628

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 600LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.7	5.6
10°-20°	136.7	15.6
20°-30°	200.3	22.9
30°-40°	209.8	24.0
40°-50°	132.6	15.1
50°-60°	71.0	8.1
60°-70°	44.6	5.1
70°-80°	25.6	2.9
80°-90°	6.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.7	44.0
0°-40°	595.5	68.0
0°-60°	799.1	91.2
0°-90°	876.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	876.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	515	49
15°	485	137
25°	437	200
35°	342	210
45°	167	133
55°	76	71
65°	45	45
75°	24	26
85°	5	7
90°	0	



TEST NUMBER: P641628

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 600LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	518.3
2.5°	517.4
5°	514.7
7.5°	509.3
10°	503.0
12.5°	494.9
15°	485.1
17.5°	474.3
20°	462.6
22.5°	449.1
25°	436.6
27.5°	420.4
30°	400.6
32.5°	375.5
35°	342.2
37.5°	301.8
40°	255.1
42.5°	208.4
45°	167.1
47.5°	134.7
50°	110.5
52.5°	91.6
55°	76.4
57.5°	66.5
60°	57.5
62.5°	50.3
65°	44.9
67.5°	39.5
70°	34.1
72.5°	29.6
75°	24.3
77.5°	18.9
80°	14.4
82.5°	9.9
85°	5.4
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)