

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641631

Luminaire Tested: ML5612LSVWFL97FS1E - 592W - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-96)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592W - 900LM - 2700K
Description: ML56 RR, MILKY OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1063.6 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641631
CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641631

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	62	58	66	61	58	56																			
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	54	48	59	53	48	58	52	48	57	52	48	46																			
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42																			
9	65	53	46	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34504
5°	34393
10°	34001
15°	33428
20°	32769
25°	32064
30°	30796
35°	27813
40°	22170
45°	15730
50°	11445
55°	8860
60°	7653
65°	7069
70°	6636
75°	6227
80°	5525
85°	4088

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15730 cd/sqm



TEST NUMBER: P641631

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.2	5.6
10°-20°	166.0	15.6
20°-30°	243.2	22.9
30°-40°	254.8	24.0
40°-50°	161.1	15.1
50°-60°	86.2	8.1
60°-70°	54.2	5.1
70°-80°	31.0	2.9
80°-90°	8.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	468.3	44.0
0°-40°	723.1	68.0
0°-60°	970.4	91.2
0°-90°	1063.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1063.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	629	
5°	625	59
15°	589	166
25°	530	243
35°	416	255
45°	203	161
55°	93	86
65°	54	54
75°	29	31
85°	6	8
90°	0	



TEST NUMBER: P641631

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	629.4
2.5°	628.3
5°	625.0
7.5°	618.4
10°	610.8
12.5°	601.0
15°	589.0
17.5°	575.9
20°	561.7
22.5°	545.4
25°	530.1
27.5°	510.5
30°	486.5
32.5°	455.9
35°	415.6
37.5°	366.5
40°	309.8
42.5°	253.0
45°	202.9
47.5°	163.6
50°	134.2
52.5°	111.3
55°	92.7
57.5°	80.7
60°	69.8
62.5°	61.1
65°	54.5
67.5°	48.0
70°	41.4
72.5°	36.0
75°	29.4
77.5°	22.9
80°	17.5
82.5°	12.0
85°	6.5
87.5°	2.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)