

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642111

Luminaire Tested: ML5612LSWFL5597FS1E - 691WB - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 691WB - 900LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 6" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1234.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642111

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642111

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	84	99	93	88	84	90	86	82	88	84	81	85	82	80	78																			
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72																			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66																			
6	85	76	69	65	84	75	69	64	73	68	64	72	67	63	70	66	63	61																			
7	81	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57																			
8	76	66	60	55	75	66	59	55	64	59	55	63	58	55	62	58	54	53																			
9	72	62	56	52	71	62	56	51	61	55	51	60	55	51	59	54	51	49																			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70702
5°	67730
10°	64322
15°	60625
20°	54803
25°	46394
30°	37778
35°	29573
40°	22020
45°	14800
50°	7164
55°	3546
60°	1798
65°	1129
70°	529
75°	466
80°	347
85°	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14800 cd/sqm



TEST NUMBER: P642111

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.2	9.3
10°-20°	297.4	24.1
20°-30°	350.4	28.4
30°-40°	276.5	22.4
40°-50°	145.1	11.8
50°-60°	37.1	3.0
60°-70°	8.9	0.7
70°-80°	2.3	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	763.0	61.8
0°-40°	1039.5	84.2
0°-60°	1221.8	99.0
0°-90°	1234.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1234.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1290	
5°	1231	115
15°	1068	297
25°	767	350
35°	442	277
45°	191	145
55°	37	37
65°	9	9
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P642111

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1289.7
2.5°	1273.3
5°	1230.8
7.5°	1190.4
10°	1155.5
12.5°	1115.1
15°	1068.2
17.5°	1009.3
20°	939.4
22.5°	856.5
25°	767.0
27.5°	677.6
30°	596.8
32.5°	517.2
35°	441.9
37.5°	372.1
40°	307.7
42.5°	247.7
45°	190.9
47.5°	127.7
50°	84.0
52.5°	56.7
55°	37.1
57.5°	24.0
60°	16.4
62.5°	12.0
65°	8.7
67.5°	5.5
70°	3.3
72.5°	2.2
75°	2.2
77.5°	2.2
80°	1.1
82.5°	1.1
85°	1.1
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)