

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642114

Luminaire Tested: ML5612LSWFL5597FS1E - 691WB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 691WB - 900LM - 4000K
Description: ML56 RR, 55D TIR OPTIC, 6" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1402.8 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642114

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642114

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93															
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85															
3	101	94	89	84	99	93	88	84	90	86	82	88	84	81	85	82	80	78				78															
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72				72															
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66															
6	85	76	69	65	84	75	69	64	73	68	64	72	67	63	70	66	63	61				61															
7	81	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57				57															
8	76	66	60	55	75	66	59	55	64	59	55	63	58	55	62	58	54	53				53															
9	72	62	56	52	71	62	56	51	61	55	51	60	55	51	59	54	51	49				49															
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80372
5°	76997
10°	73123
15°	68916
20°	62305
25°	52745
30°	42950
35°	33622
40°	25033
45°	16831
50°	8145
55°	4033
60°	2039
65°	1284
70°	593
75°	530
80°	379
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16831 cd/sqm



TEST NUMBER: P642114

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.9	9.3
10°-20°	338.1	24.1
20°-30°	398.4	28.4
30°-40°	314.4	22.4
40°-50°	165.0	11.8
50°-60°	42.2	3.0
60°-70°	10.0	0.7
70°-80°	2.6	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	867.4	61.8
0°-40°	1181.8	84.2
0°-60°	1388.9	99.0
0°-90°	1402.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1402.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1466	
5°	1399	131
15°	1214	338
25°	872	398
35°	502	314
45°	217	165
55°	42	42
65°	10	10
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P642114

CATALOG NUMBER: ML5612LSWFL5597FS1E - 691WB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1466.1
2.5°	1447.5
5°	1399.2
7.5°	1353.3
10°	1313.6
12.5°	1267.7
15°	1214.3
17.5°	1147.4
20°	1068.0
22.5°	973.7
25°	872.0
27.5°	770.3
30°	678.5
32.5°	587.9
35°	502.4
37.5°	423.0
40°	349.8
42.5°	281.6
45°	217.1
47.5°	145.1
50°	95.5
52.5°	64.5
55°	42.2
57.5°	27.3
60°	18.6
62.5°	13.6
65°	9.9
67.5°	6.2
70°	3.7
72.5°	2.5
75°	2.5
77.5°	2.5
80°	1.2
82.5°	1.2
85°	1.2
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)