

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642120

Luminaire Tested: ML5612LSWFL5597FS1E - 692H - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-61)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 692H - 1200LM - 5000K
Description: ML56 RR, 55D TIR OPTIC, 6" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1692.8 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642120
CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642120

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																											
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																											
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79																											
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73																											
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67																											
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62																											
7	81	71	65	61	80	71	65	60	69	64	60	68	63	60	67	63	59	58																											
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54																											
9	73	63	57	52	72	62	56	52	61	56	52	60	56	52	60	55	52	50																											
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99515
5°	95432
10°	90095
15°	84779
20°	76622
25°	65084
30°	53078
35°	41432
40°	30650
45°	19925
50°	8204
55°	3164
60°	1480
65°	389
70°	240
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19925 cd/sqm



TEST NUMBER: P642120

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.9	9.6
10°-20°	415.8	24.6
20°-30°	491.9	29.1
30°-40°	387.3	22.9
40°-50°	195.0	11.5
50°-60°	35.9	2.1
60°-70°	4.4	0.3
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1069.6	63.2
0°-40°	1456.8	86.1
0°-60°	1687.8	99.7
0°-90°	1692.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1692.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1815	
5°	1734	162
15°	1494	416
25°	1076	492
35°	619	387
45°	257	195
55°	33	36
65°	3	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P642120

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1815.3
2.5°	1794.3
5°	1734.2
7.5°	1672.6
10°	1618.5
12.5°	1559.9
15°	1493.8
17.5°	1409.6
20°	1313.4
22.5°	1200.7
25°	1076.0
27.5°	954.3
30°	838.5
32.5°	727.3
35°	619.1
37.5°	518.5
40°	428.3
42.5°	339.6
45°	257.0
47.5°	166.8
50°	96.2
52.5°	52.6
55°	33.1
57.5°	22.5
60°	13.5
62.5°	6.0
65°	3.0
67.5°	1.5
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)