

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641660

Luminaire Tested: ML5612LSVWFL97FS1E - 593SNB - 600LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641660  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-99)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 593SNB - 600LM - 5000K  
Description: ML56 RR, MILKY OPTIC, 5" SATIN NICKLE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 811.0 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641660  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 593SNB - 600LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641660

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593SNB - 600LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																			
3	99	91	85	81	97	90	84	80	87	82	79	84	81	77	82	79	76	74																			
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61																			
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51																			
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	50	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43																			
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	42060
5°	41911
10°	41618
15°	41247
20°	40693
25°	39840
30°	38248
35°	34288
40°	26700
45°	17918
50°	11041
55°	6647
60°	3963
65°	2354
70°	1339
75°	1190
80°	864
85°	906

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17918 cd/sqm



TEST NUMBER: P641660

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593SNB - 600LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.2	6.2
10°-20°	142.2	17.5
20°-30°	210.0	25.9
30°-40°	217.9	26.9
40°-50°	126.5	15.6
50°-60°	45.9	5.7
60°-70°	13.3	1.6
70°-80°	4.1	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	402.4	49.6
0°-40°	620.3	76.5
0°-60°	792.8	97.8
0°-90°	811.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	811.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	533	
5°	529	50
15°	505	142
25°	457	210
35°	356	218
45°	160	127
55°	48	46
65°	13	13
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P641660

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593SNB - 600LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	532.8
2.5°	531.8
5°	528.9
7.5°	525.0
10°	519.2
12.5°	512.5
15°	504.7
17.5°	495.1
20°	484.4
22.5°	471.9
25°	457.4
27.5°	440.9
30°	419.6
32.5°	392.6
35°	355.8
37.5°	312.3
40°	259.1
42.5°	206.9
45°	160.5
47.5°	120.9
50°	89.9
52.5°	66.7
55°	48.3
57.5°	34.8
60°	25.1
62.5°	17.4
65°	12.6
67.5°	8.7
70°	5.8
72.5°	4.8
75°	3.9
77.5°	2.9
80°	1.9
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)