

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642138

Luminaire Tested: ML5612LSWFL5597FS1E - 692SC - 600LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642138
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 692SC - 600LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 6" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1017.1 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.81
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642138
CATALOG NUMBER: ML5612LSWFL5597FS1E - 692SC - 600LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642138

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692SC - 600LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	85	91	87	84	88	85	82	86	83	81	79																			
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	74	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72730
5°	63510
10°	55738
15°	51419
20°	45883
25°	38766
30°	31518
35°	24541
40°	18077
45°	11707
50°	4827
55°	1806
60°	789
65°	233
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11707 cd/sqm



TEST NUMBER: P642138

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692SC - 600LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	10.4
10°-20°	252.2	24.8
20°-30°	292.8	28.8
30°-40°	229.4	22.6
40°-50°	114.8	11.3
50°-60°	20.3	2.0
60°-70°	2.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.6	64.0
0°-40°	880.0	86.5
0°-60°	1015.2	99.8
0°-90°	1017.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1017.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1327	
5°	1154	106
15°	906	252
25°	641	293
35°	367	229
45°	151	115
55°	19	20
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642138

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692SC - 600LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1326.7
2.5°	1276.3
5°	1154.1
7.5°	1059.7
10°	1001.3
12.5°	955.4
15°	906.0
17.5°	847.6
20°	786.5
22.5°	715.5
25°	640.9
27.5°	566.3
30°	497.9
32.5°	431.4
35°	366.7
37.5°	306.5
40°	252.6
42.5°	200.4
45°	151.0
47.5°	98.0
50°	56.6
52.5°	29.7
55°	18.9
57.5°	11.7
60°	7.2
62.5°	2.7
65°	1.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)