

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642151

Luminaire Tested: ML5612LSWFL5597FS1E - 692W - 600LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642151
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-62)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 692W - 600LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 961.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642151
CATALOG NUMBER: ML5612LSWFL5597FS1E - 692W - 600LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642151
 CATALOG NUMBER: ML5612LSWFL5597FS1E - 692W - 600LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79																			
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72																			
5	90	81	75	71	89	80	75	70	79	73	70	77	72	69	75	71	68	67																			
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62																			
7	81	71	65	60	79	70	64	60	69	63	60	68	63	59	67	62	59	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51	50																			
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55412
5°	53148
10°	50305
15°	47475
20°	43001
25°	36613
30°	29922
35°	23383
40°	17340
45°	11335
50°	4861
55°	2036
60°	1118
65°	662
70°	545
75°	551
80°	537
85°	566

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11335 cd/sqm



TEST NUMBER: P642151

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692W - 600LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.3	9.4
10°-20°	232.9	24.2
20°-30°	276.5	28.8
30°-40°	218.9	22.8
40°-50°	111.3	11.6
50°-60°	22.6	2.4
60°-70°	5.4	0.6
70°-80°	2.5	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.6	62.4
0°-40°	818.5	85.2
0°-60°	952.4	99.1
0°-90°	961.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	961.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1011	
5°	966	90
15°	836	233
25°	605	276
35°	349	219
45°	146	111
55°	21	23
65°	5	5
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P642151

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692W - 600LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1010.8
2.5°	998.9
5°	965.8
7.5°	933.5
10°	903.7
12.5°	873.1
15°	836.5
17.5°	789.8
20°	737.1
22.5°	674.2
25°	605.3
27.5°	536.4
30°	472.7
32.5°	410.6
35°	349.4
37.5°	294.1
40°	242.3
42.5°	193.0
45°	146.2
47.5°	96.1
50°	57.0
52.5°	32.3
55°	21.3
57.5°	15.3
60°	10.2
62.5°	6.8
65°	5.1
67.5°	3.4
70°	3.4
72.5°	2.6
75°	2.6
77.5°	1.7
80°	1.7
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)