

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641703

Luminaire Tested: ML5612LSVWFL97FS1E - 594SNB - 600LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-102)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 594SNB - 600LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 969.5 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.26
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641703
CATALOG NUMBER: ML5612LSVWFL97FS1E - 594SNB - 600LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P641703

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594SNB - 600LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	85	82	78	83	79	76	74																			
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64																			
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56																			
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49																			
6	74	61	53	47	72	60	53	47	59	52	46	57	51	46	56	50	46	44																			
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41	39																			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35																			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32																			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34434
5°	34423
10°	34252
15°	33892
20°	33477
25°	32759
30°	31749
35°	30453
40°	28586
45°	26258
50°	23592
55°	20631
60°	17430
65°	14588
70°	12233
75°	10401
80°	8956
85°	8967

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26258 cd/sqm



TEST NUMBER: P641703

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594SNB - 600LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.2	4.3
10°-20°	116.9	12.1
20°-30°	173.0	17.8
30°-40°	196.8	20.3
40°-50°	181.1	18.7
50°-60°	134.1	13.8
60°-70°	78.5	8.1
70°-80°	36.8	3.8
80°-90°	11.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.2	34.2
0°-40°	528.0	54.5
0°-60°	843.2	87.0
0°-90°	969.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	436	
5°	434	41
15°	415	117
25°	376	173
35°	316	197
45°	235	181
55°	150	134
65°	78	78
75°	34	37
85°	10	11
90°	0	



TEST NUMBER: P641703

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594SNB - 600LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	436.2
2.5°	435.3
5°	434.4
7.5°	431.7
10°	427.3
12.5°	421.9
15°	414.7
17.5°	406.6
20°	398.5
22.5°	387.8
25°	376.1
27.5°	363.5
30°	348.3
32.5°	333.0
35°	316.0
37.5°	297.1
40°	277.4
42.5°	256.7
45°	235.2
47.5°	213.6
50°	192.1
52.5°	170.5
55°	149.9
57.5°	129.3
60°	110.4
62.5°	93.3
65°	78.1
67.5°	64.6
70°	53.0
72.5°	43.1
75°	34.1
77.5°	26.0
80°	19.7
82.5°	14.4
85°	9.9
87.5°	6.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)