

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641726

Luminaire Tested: ML5612LSVWFL97FS1E - 594WB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-101)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 594WB - 1200LM - 2700K
Description: ML56 RR, MILKY OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1448.8 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641726

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641726

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	94	88	82	99	92	86	82	88	84	80	85	81	78	82	79	76	74																			
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64																			
4	86	75	67	60	84	73	66	60	71	64	59	69	63	58	67	62	58	56																			
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	60	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	56	47	42	67	55	47	41	53	46	41	52	46	41	51	45	41	39																			
8	64	51	43	37	62	50	43	37	49	42	37	48	41	37	47	41	37	35																			
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31																			
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50041
5°	50026
10°	49859
15°	49542
20°	49144
25°	48315
30°	47071
35°	45313
40°	42735
45°	39509
50°	35517
55°	31269
60°	26477
65°	22452
70°	18903
75°	16104
80°	14411
85°	13133

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 39509 cd/sqm



TEST NUMBER: P641726

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	4.1
10°-20°	171.1	11.8
20°-30°	255.2	17.6
30°-40°	292.8	20.2
40°-50°	271.9	18.8
50°-60°	203.1	14.0
60°-70°	120.2	8.3
70°-80°	57.8	4.0
80°-90°	16.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.3	33.6
0°-40°	779.0	53.8
0°-60°	1254.0	86.5
0°-90°	1448.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1448.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	634	
5°	631	60
15°	606	171
25°	555	255
35°	470	293
45°	354	272
55°	227	203
65°	120	120
75°	53	58
85°	14	17
90°	0	



TEST NUMBER: P641726

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	633.9
2.5°	633.9
5°	631.3
7.5°	627.3
10°	622.0
12.5°	615.4
15°	606.2
17.5°	596.9
20°	585.0
22.5°	570.5
25°	554.7
27.5°	537.5
30°	516.4
32.5°	493.9
35°	470.2
37.5°	442.4
40°	414.7
42.5°	384.3
45°	353.9
47.5°	320.9
50°	289.2
52.5°	257.5
55°	227.2
57.5°	196.8
60°	167.7
62.5°	142.6
65°	120.2
67.5°	99.0
70°	81.9
72.5°	67.4
75°	52.8
77.5°	42.3
80°	31.7
82.5°	22.5
85°	14.5
87.5°	9.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)