

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642199

Luminaire Tested: ML5612LSWFL5597FS1E - 693TBZB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-66)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 693TBZB - 600LM - 4000K
Description: ML56 RR, 55D TIR OPTIC, 6" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1072.1 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642199

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693TBZB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642199

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693TBZB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93					93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86					86			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	60	69	64	60	68	63	60	67	63	59	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54					54			
9	73	63	57	52	72	62	56	52	61	56	52	60	56	52	60	55	52	50					50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47					47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62539
5°	59955
10°	56829
15°	53553
20°	48503
25°	41283
30°	33784
35°	26334
40°	19508
45°	12668
50°	5279
55°	1940
60°	844
65°	246
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12668 cd/sqm



TEST NUMBER: P642199

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693TBZB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	9.5
10°-20°	262.8	24.5
20°-30°	312.0	29.1
30°-40°	246.4	23.0
40°-50°	124.1	11.6
50°-60°	22.4	2.1
60°-70°	2.6	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.7	63.1
0°-40°	923.1	86.1
0°-60°	1069.5	99.8
0°-90°	1072.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1072.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1141	
5°	1090	102
15°	944	263
25°	682	312
35°	394	246
45°	163	124
55°	20	22
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642199

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693TBZB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1140.8
2.5°	1127.2
5°	1089.5
7.5°	1053.8
10°	1020.9
12.5°	984.2
15°	943.6
17.5°	892.3
20°	831.4
22.5°	761.8
25°	682.5
27.5°	605.2
30°	533.7
32.5°	462.1
35°	393.5
37.5°	330.6
40°	272.6
42.5°	216.6
45°	163.4
47.5°	105.4
50°	61.9
52.5°	32.9
55°	20.3
57.5°	13.5
60°	7.7
62.5°	3.9
65°	1.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)