

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642215

Luminaire Tested: ML5612LSWFL5597FS1E - 693WB - 600LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642215  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-63)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSWFL5597FS1E - 693WB - 600LM - 5000K  
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1091.9 lumens  
Efficiency: N/A  
Efficacy: 106.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642215  
CATALOG NUMBER: ML5612LSWFL5597FS1E - 693WB - 600LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642215

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693WB - 600LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93																
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85																
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78			78																
4	96	87	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72																
5	90	81	75	71	89	80	75	70	79	73	70	77	72	69	75	71	68	67			67																
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	67	63	62			62																
7	81	71	64	60	79	70	64	60	69	63	59	68	63	59	66	62	59	57			57																
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53																
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51	50			50																
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47			47																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	62862
5°	60230
10°	57158
15°	53831
20°	48794
25°	41525
30°	33967
35°	26595
40°	19723
45°	12970
50°	5603
55°	2313
60°	1272
65°	623
70°	625
75°	614
80°	600
85°	629

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12970 cd/sqm



TEST NUMBER: P642215

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693WB - 600LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.4	9.4
10°-20°	264.2	24.2
20°-30°	313.8	28.7
30°-40°	248.7	22.8
40°-50°	126.8	11.6
50°-60°	25.8	2.4
60°-70°	5.7	0.5
70°-80°	3.1	0.3
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.4	62.3
0°-40°	929.1	85.1
0°-60°	1081.8	99.1
0°-90°	1091.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1091.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1147	
5°	1094	102
15°	948	264
25°	686	314
35°	397	249
45°	167	127
55°	24	26
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P642215

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693WB - 600LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1146.7
2.5°	1132.2
5°	1094.5
7.5°	1058.7
10°	1026.8
12.5°	990.1
15°	948.5
17.5°	896.3
20°	836.4
22.5°	765.8
25°	686.5
27.5°	609.1
30°	536.6
32.5°	466.0
35°	397.4
37.5°	334.5
40°	275.6
42.5°	219.5
45°	167.3
47.5°	109.3
50°	65.7
52.5°	36.7
55°	24.2
57.5°	17.4
60°	11.6
62.5°	6.8
65°	4.8
67.5°	3.9
70°	3.9
72.5°	2.9
75°	2.9
77.5°	2.9
80°	1.9
82.5°	1.9
85°	1.0
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)