

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642222

Luminaire Tested: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642222  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-68)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3000K  
Description: ML56 RR, 55D TIR OPTIC, 6" TUSCON BRONZE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1546.0 lumens  
Efficiency: N/A  
Efficacy: 93.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642222

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642222

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																											
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85																											
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																											
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																											
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																											
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61																											
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																											
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53																											
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49																											
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	88091
5°	84465
10°	80148
15°	75778
20°	68623
25°	58171
30°	47033
35°	36540
40°	27022
45°	17800
50°	8571
55°	4540
60°	2982
65°	2465
70°	1955
75°	1440
80°	852
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17800 cd/sqm



TEST NUMBER: P642222

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.6	9.3
10°-20°	371.6	24.0
20°-30°	438.8	28.4
30°-40°	342.1	22.1
40°-50°	175.0	11.3
50°-60°	47.5	3.1
60°-70°	19.3	1.2
70°-80°	7.3	0.5
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.0	61.7
0°-40°	1296.0	83.8
0°-60°	1518.6	98.2
0°-90°	1546.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1546.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1607	
5°	1535	144
15°	1335	372
25°	962	439
35°	546	342
45°	230	175
55°	48	48
65°	19	19
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P642222

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1606.9
2.5°	1587.9
5°	1534.9
7.5°	1484.6
10°	1439.8
12.5°	1392.3
15°	1335.2
17.5°	1261.9
20°	1176.3
22.5°	1073.1
25°	961.7
27.5°	848.9
30°	743.0
32.5°	642.5
35°	546.0
37.5°	457.8
40°	377.6
42.5°	300.2
45°	229.6
47.5°	150.8
50°	100.5
52.5°	67.9
55°	47.5
57.5°	35.3
60°	27.2
62.5°	23.1
65°	19.0
67.5°	16.3
70°	12.2
72.5°	9.5
75°	6.8
77.5°	4.1
80°	2.7
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)