

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642223

Luminaire Tested: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642223
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-68)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 6" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1588.1 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642223
CATALOG NUMBER: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642223

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																																				
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85																																				
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																																				
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																																				
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																																				
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61																																				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																																				
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53																																				
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49																																				
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90486
5°	86765
10°	82330
15°	77844
20°	70490
25°	59755
30°	48311
35°	37537
40°	27759
45°	18281
50°	8810
55°	4664
60°	3059
65°	2529
70°	2020
75°	1483
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18281 cd/sqm



TEST NUMBER: P642223

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	9.3
10°-20°	381.7	24.0
20°-30°	450.7	28.4
30°-40°	351.4	22.1
40°-50°	179.8	11.3
50°-60°	48.8	3.1
60°-70°	19.8	1.2
70°-80°	7.6	0.5
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	980.0	61.7
0°-40°	1331.3	83.8
0°-60°	1560.0	98.2
0°-90°	1588.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1588.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1651	
5°	1577	147
15°	1372	382
25°	988	451
35°	561	351
45°	236	180
55°	49	49
65°	20	20
75°	7	8
85°	0	1
90°	0	



TEST NUMBER: P642223

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694TBZB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1650.6
2.5°	1631.1
5°	1576.7
7.5°	1525.1
10°	1479.0
12.5°	1430.2
15°	1371.6
17.5°	1296.2
20°	1208.3
22.5°	1102.3
25°	987.9
27.5°	872.1
30°	763.2
32.5°	660.0
35°	560.9
37.5°	470.2
40°	387.9
42.5°	308.4
45°	235.8
47.5°	154.9
50°	103.3
52.5°	69.8
55°	48.8
57.5°	36.3
60°	27.9
62.5°	23.7
65°	19.5
67.5°	16.7
70°	12.6
72.5°	9.8
75°	7.0
77.5°	4.2
80°	2.8
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)