

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641778

Luminaire Tested: ML5612LSVWFL97FS1E - 692H - 600LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-107)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 692H - 600LM - 3500K
Description: ML56 RR, MILKY OPTIC, 6" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 876.1 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.1
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641778

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692H - 600LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P641778

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692H - 600LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75																			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	67																			
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61																			
6	81	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	57	56																			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51																			
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	52	46	42	52	46	42	51	45	41	50	45	41	40																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35162
5°	34801
10°	33806
15°	32174
20°	30289
25°	28363
30°	26441
35°	24407
40°	20961
45°	15040
50°	9117
55°	5152
60°	2763
65°	1284
70°	721
75°	572
80°	284
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15040 cd/sqm



TEST NUMBER: P641778

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692H - 600LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.6	6.8
10°-20°	159.0	18.2
20°-30°	215.6	24.6
30°-40°	225.6	25.7
40°-50°	150.1	17.1
50°-60°	51.6	5.9
60°-70°	11.6	1.3
70°-80°	2.6	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.2	49.6
0°-40°	659.8	75.3
0°-60°	861.5	98.3
0°-90°	876.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	876.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	641	
5°	632	60
15°	567	159
25°	469	216
35°	365	226
45°	194	150
55°	54	52
65°	10	12
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P641778

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692H - 600LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	641.4
2.5°	639.6
5°	632.4
7.5°	621.7
10°	607.3
12.5°	588.4
15°	566.9
17.5°	543.5
20°	519.2
22.5°	494.1
25°	468.9
27.5°	443.8
30°	417.7
32.5°	392.6
35°	364.7
37.5°	333.3
40°	292.9
42.5°	245.3
45°	194.0
47.5°	146.4
50°	106.9
52.5°	76.4
55°	53.9
57.5°	36.8
60°	25.2
62.5°	16.2
65°	9.9
67.5°	6.3
70°	4.5
72.5°	2.7
75°	2.7
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)