

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642250

Luminaire Tested: ML5612LSWFL5597FS1E - 694WB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-67)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 694WB - 900LM - 5000K
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1410.8 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642250
CATALOG NUMBER: ML5612LSWFL5597FS1E - 694WB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642250

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694WB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																											
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85																											
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78																											
4	95	87	81	76	93	86	80	76	84	79	75	81	77	74	80	76	73	72																											
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																											
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	63	61																											
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57																											
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53																											
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49																											
10	69	58	52	48	68	58	52	48	57	51	48	56	51	48	55	51	47	46																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80608
5°	76953
10°	73078
15°	69081
20°	62545
25°	52987
30°	42886
35°	33301
40°	24596
45°	16164
50°	7829
55°	4148
60°	2862
65°	2257
70°	1988
75°	1313
80°	789
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16164 cd/sqm



TEST NUMBER: P642250

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694WB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.9	9.3
10°-20°	338.7	24.0
20°-30°	400.2	28.4
30°-40°	312.1	22.1
40°-50°	159.5	11.3
50°-60°	43.6	3.1
60°-70°	17.9	1.3
70°-80°	7.2	0.5
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	869.8	61.7
0°-40°	1181.9	83.8
0°-60°	1385.0	98.2
0°-90°	1410.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1410.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1470	
5°	1398	131
15°	1217	339
25°	876	400
35°	498	312
45°	208	160
55°	43	44
65°	17	18
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P642250

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694WB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1470.4
2.5°	1453.0
5°	1398.4
7.5°	1352.5
10°	1312.8
12.5°	1268.1
15°	1217.2
17.5°	1150.2
20°	1072.1
22.5°	980.2
25°	876.0
27.5°	774.3
30°	677.5
32.5°	586.9
35°	497.6
37.5°	418.2
40°	343.7
42.5°	274.2
45°	208.5
47.5°	137.7
50°	91.8
52.5°	62.0
55°	43.4
57.5°	32.3
60°	26.1
62.5°	21.1
65°	17.4
67.5°	14.9
70°	12.4
72.5°	8.7
75°	6.2
77.5°	5.0
80°	2.5
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)