

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641800

Luminaire Tested: ML5612LSVWFL97FS1E - 692SC - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-106)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 692SC - 900LM - 5000K
Description: ML56 RR, MILKY OPTIC, 6" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1285.5 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641800
CATALOG NUMBER: ML5612LSVWFL97FS1E - 692SC - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641800

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692SC - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 93 | | | 93 | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 97 | 93 | 105 | 100 | 96 | 92 | 97 | 93 | 90 | 93 | 91 | 88 | 91 | 89 | 87 | 85 | | | 85 | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 85 | 82 | 87 | 84 | 81 | 85 | 82 | 79 | 78 | | | 78 | | | | | | | | | | | | | | | | |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 83 | 79 | 75 | 81 | 77 | 74 | 79 | 76 | 73 | 71 | | | 71 | | | | | | | | | | | | | | | | |
| 5 | 90 | 81 | 74 | 70 | 88 | 80 | 74 | 69 | 78 | 73 | 69 | 76 | 72 | 68 | 74 | 71 | 67 | 66 | | | 66 | | | | | | | | | | | | | | | | |
| 6 | 85 | 75 | 69 | 64 | 83 | 74 | 68 | 64 | 73 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 62 | 61 | | | 61 | | | | | | | | | | | | | | | | |
| 7 | 80 | 70 | 64 | 59 | 79 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | 56 | | | | | | | | | | | | | | | | |
| 8 | 76 | 66 | 59 | 55 | 75 | 65 | 59 | 55 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 52 | | | 52 | | | | | | | | | | | | | | | | |
| 9 | 72 | 62 | 55 | 51 | 71 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 58 | 54 | 50 | 49 | | | 49 | | | | | | | | | | | | | | | | |
| 10 | 68 | 58 | 52 | 48 | 67 | 58 | 52 | 48 | 57 | 51 | 48 | 56 | 51 | 47 | 55 | 51 | 47 | 46 | | | 46 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 99992 |
| 5° | 93473 |
| 10° | 76446 |
| 15° | 58139 |
| 20° | 46432 |
| 25° | 39577 |
| 30° | 34815 |
| 35° | 31079 |
| 40° | 26478 |
| 45° | 18676 |
| 50° | 10908 |
| 55° | 5696 |
| 60° | 2588 |
| 65° | 804 |
| 70° | 192 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18676 cd/sqm



TEST NUMBER: P641800

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692SC - 900LM - 5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 151.6 | 11.8 |
| 10°-20° | 288.8 | 22.5 |
| 20°-30° | 302.9 | 23.6 |
| 30°-40° | 288.9 | 22.5 |
| 40°-50° | 186.4 | 14.5 |
| 50°-60° | 57.9 | 4.5 |
| 60°-70° | 8.5 | 0.7 |
| 70°-80° | 0.5 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 743.3 | 57.8 |
| 0°-40° | 1032.2 | 80.3 |
| 0°-60° | 1276.5 | 99.3 |
| 0°-90° | 1285.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1285.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1824 | |
| 5° | 1699 | 152 |
| 15° | 1024 | 289 |
| 25° | 654 | 303 |
| 35° | 464 | 289 |
| 45° | 241 | 186 |
| 55° | 60 | 58 |
| 65° | 6 | 8 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P641800

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692SC - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1824.0 |
| 2.5° | 1791.7 |
| 5° | 1698.6 |
| 7.5° | 1550.8 |
| 10° | 1373.3 |
| 12.5° | 1188.3 |
| 15° | 1024.4 |
| 17.5° | 896.5 |
| 20° | 795.9 |
| 22.5° | 718.9 |
| 25° | 654.3 |
| 27.5° | 599.7 |
| 30° | 550.0 |
| 32.5° | 506.6 |
| 35° | 464.4 |
| 37.5° | 422.2 |
| 40° | 370.0 |
| 42.5° | 307.9 |
| 45° | 240.9 |
| 47.5° | 178.8 |
| 50° | 127.9 |
| 52.5° | 88.2 |
| 55° | 59.6 |
| 57.5° | 38.5 |
| 60° | 23.6 |
| 62.5° | 13.7 |
| 65° | 6.2 |
| 67.5° | 2.5 |
| 70° | 1.2 |
| 72.5° | 1.2 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)