

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642288

Luminaire Tested: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642288  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-129)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K  
Description: ML56 RR, WW OPTIC, 5" WW INSERT WITH SPECULAR CLEAR TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 582.5 lumens  
Efficiency: N/A  
Efficacy: 56.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.26  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642288

CATALOG NUMBER: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P642288

CATALOG NUMBER: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88	88	88	88	88	88		
	2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76	76	76	76	76	76		
	3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66	66	66	66	66	66		
	4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58	58	58	58	58	58		
	5	80	69	61	55	78	68	60	54	66	59	54	64	58	53	62	57	53	51	51	51	51	51	51		
	6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45	45	45	45	45	45		
	7	69	57	49	43	68	56	48	43	55	48	43	53	47	42	52	46	42	40	40	40	40	40	40		
	8	65	52	44	39	63	52	44	39	50	43	38	49	43	38	48	42	38	36	36	36	36	36	36		
	9	61	48	40	35	59	48	40	35	46	40	35	45	39	35	44	39	35	33	33	33	33	33	33		
	10	57	45	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30	30	30	30	30	30		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	21496	21496	21496	21496	21496
5°	21506	21506	21435	21506	21506
10°	21322	21250	21250	21250	21322
15°	21298	21151	20930	20930	21077
20°	21363	20985	20531	20531	20607
25°	21209	20669	19964	19885	19964
30°	20728	20154	19252	19170	19252
35°	20006	19226	18185	18272	18358
40°	18982	18147	17044	17137	17230
45°	17561	16757	15652	15652	15953
50°	16223	15339	14123	13792	14013
55°	14836	13859	12497	11506	11258
60°	13199	12346	10783	8936	7373
65°	11749	10740	8723	5884	3530
70°	10363	9117	6440	2908	1039
75°	8510	7137	3843	824	275
80°	6546	4910	1637	0	0
85°	3261	2446	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 10°  
 Vertical Angle: 45°  
 Luminance: 17661 cd/sqm



TEST NUMBER: P642288

CATALOG NUMBER: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.7	4.4
10°-20°	72.6	12.5
20°-30°	107.1	18.4
30°-40°	121.2	20.8
40°-50°	112.0	19.2
50°-60°	82.7	14.2
60°-70°	44.5	7.6
70°-80°	14.9	2.6
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.4	35.3
0°-40°	326.6	56.1
0°-60°	521.3	89.5
0°-90°	582.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	582.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	272	272	272	272	272	
5°	271	271	270	271	271	26
15°	261	259	256	256	258	74
25°	244	237	229	228	229	112
35°	208	200	189	190	190	129
45°	157	150	140	140	143	122
55°	108	101	91	84	82	96
65°	63	58	47	32	19	63
75°	28	23	13	3	1	30
85°	4	3	0	0	0	5
90°	0	0	0	0	0	



TEST NUMBER: P642288

CATALOG NUMBER: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3
2.5°	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3
5°	271.4	271.4	270.5	271.4	271.4	271.4	271.4	270.5	271.4	271.4	271.4
7.5°	269.6	268.7	268.7	268.7	268.7	268.7	268.7	268.7	268.7	268.7	268.7
10°	266.0	266.0	266.0	266.0	266.0	266.0	266.0	266.0	266.0	266.0	265.1
12.5°	264.2	263.3	263.3	263.3	263.3	263.3	263.3	262.4	263.3	262.4	262.4
15°	260.6	260.6	260.6	260.6	260.6	260.6	259.7	259.7	259.7	259.7	258.8
17.5°	257.0	257.0	257.9	257.9	257.0	257.0	257.0	256.1	255.2	255.2	254.3
20°	254.3	254.3	253.4	253.4	252.5	253.4	252.5	251.6	251.6	250.7	249.8
22.5°	248.9	248.9	248.9	248.9	248.9	248.0	248.0	247.1	246.2	245.3	243.5
25°	243.5	243.5	243.5	243.5	242.6	242.6	242.6	240.9	240.0	239.1	237.3
27.5°	237.3	236.4	236.4	236.4	235.5	235.5	234.6	233.7	232.8	231.9	231.0
30°	227.4	227.4	227.4	227.4	226.5	225.6	225.6	224.7	223.8	222.0	221.1
32.5°	218.4	218.4	217.5	216.6	216.6	216.6	215.7	214.8	213.0	212.1	210.3
35°	207.6	206.7	206.7	205.8	205.8	205.8	204.9	203.1	202.2	201.3	199.5
37.5°	195.0	195.9	195.0	195.0	194.1	193.2	192.3	191.4	190.5	188.7	186.9
40°	184.2	184.2	183.3	182.4	181.5	181.5	180.6	179.7	178.8	177.9	176.1
42.5°	171.7	171.7	170.8	170.8	169.9	169.9	168.1	167.2	166.3	165.4	162.7
45°	157.3	157.3	158.2	157.3	156.4	155.5	155.5	154.6	152.8	151.9	150.1
47.5°	144.7	145.6	144.7	143.8	143.8	142.9	142.9	141.1	141.1	139.3	138.4
50°	132.1	132.1	132.1	132.1	131.2	130.3	130.3	129.4	127.6	126.7	124.9
52.5°	119.5	119.5	119.5	119.5	118.6	118.6	117.7	116.8	115.9	114.1	112.3
55°	107.8	106.9	106.9	106.9	106.0	106.0	105.1	104.2	103.4	102.5	100.7
57.5°	96.2	95.3	95.3	94.4	94.4	93.5	93.5	92.6	91.7	89.9	89.0
60°	83.6	84.5	83.6	83.6	82.7	82.7	82.7	81.8	80.0	79.1	78.2
62.5°	72.8	73.7	72.8	71.9	71.9	71.9	71.9	70.1	69.2	68.3	67.4
65°	62.9	62.9	62.9	62.0	62.0	62.0	60.2	60.2	59.3	58.4	57.5
67.5°	53.9	53.0	53.0	53.0	52.1	52.1	51.2	51.2	49.4	49.4	47.6
70°	44.9	44.0	44.0	44.0	43.1	42.2	43.1	41.3	40.4	39.5	39.5
72.5°	35.9	35.9	35.0	35.0	35.0	34.2	34.2	33.3	32.4	31.5	30.6
75°	27.9	27.9	27.9	27.0	27.0	26.1	26.1	25.2	25.2	23.4	23.4
77.5°	20.7	20.7	20.7	19.8	19.8	19.8	18.9	18.9	18.0	17.1	16.2
80°	14.4	13.5	13.5	13.5	13.5	12.6	12.6	12.6	11.7	11.7	10.8
82.5°	8.1	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3
85°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.7	2.7	2.7
87.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P642288

CATALOG NUMBER: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3
2.5°	272.3	272.3	272.3	272.3	271.4	272.3	271.4	272.3	272.3	272.3	272.3
5°	271.4	270.5	270.5	270.5	271.4	271.4	270.5	270.5	270.5	270.5	270.5
7.5°	268.7	268.7	268.7	267.8	268.7	268.7	267.8	268.7	268.7	267.8	268.7
10°	266.0	266.0	265.1	265.1	265.1	265.1	265.1	265.1	264.2	265.1	265.1
12.5°	262.4	262.4	262.4	261.5	261.5	261.5	261.5	261.5	260.6	260.6	261.5
15°	258.8	258.8	257.9	257.9	257.9	257.0	257.0	257.0	257.0	256.1	256.1
17.5°	254.3	253.4	253.4	252.5	252.5	251.6	251.6	250.7	250.7	250.7	249.8
20°	248.9	248.0	247.1	247.1	246.2	246.2	245.3	245.3	244.4	244.4	243.5
22.5°	242.6	241.7	240.9	240.0	240.0	239.1	239.1	238.2	237.3	236.4	236.4
25°	237.3	235.5	234.6	233.7	231.9	231.9	231.0	231.0	230.1	229.2	228.3
27.5°	229.2	227.4	226.5	225.6	224.7	223.8	222.0	222.0	221.1	220.2	219.3
30°	219.3	218.4	216.6	215.7	214.8	214.8	213.0	211.2	211.2	211.2	210.3
32.5°	209.4	207.6	206.7	204.9	204.0	204.0	203.1	201.3	200.4	200.4	199.5
35°	198.6	196.8	195.0	194.1	193.2	192.3	191.4	190.5	189.6	188.7	187.8
37.5°	186.0	184.2	183.3	182.4	181.5	180.6	179.7	178.8	177.9	177.0	177.9
40°	174.3	172.5	170.8	169.9	169.0	169.0	168.1	167.2	166.3	165.4	165.4
42.5°	161.8	160.0	159.1	158.2	157.3	156.4	155.5	154.6	153.7	153.7	152.8
45°	148.3	147.4	145.6	144.7	143.8	143.8	142.0	141.1	141.1	140.2	140.2
47.5°	136.6	134.8	133.0	132.1	131.2	130.3	129.4	128.5	127.6	127.6	127.6
50°	123.1	122.2	120.4	119.5	118.6	118.6	117.7	116.8	115.9	115.0	115.0
52.5°	110.5	109.6	109.6	107.8	106.9	106.9	105.1	105.1	103.4	102.5	101.6
55°	99.8	98.0	97.1	95.3	95.3	94.4	93.5	92.6	91.7	90.8	89.9
57.5°	87.2	86.3	85.4	84.5	84.5	83.6	82.7	81.8	80.0	80.0	78.2
60°	77.3	75.5	74.6	73.7	72.8	72.8	71.9	71.0	69.2	68.3	67.4
62.5°	66.5	64.7	64.7	63.8	62.0	62.0	61.1	59.3	58.4	56.6	55.7
65°	56.6	55.7	53.9	53.0	53.0	52.1	50.3	49.4	48.5	46.7	44.9
67.5°	46.7	45.8	44.9	43.1	43.1	42.2	40.4	39.5	37.7	36.8	35.0
70°	37.7	36.8	35.9	34.2	34.2	33.3	32.4	30.6	28.8	27.9	26.1
72.5°	29.7	28.8	27.9	26.1	26.1	25.2	23.4	22.5	20.7	18.9	18.0
75°	22.5	21.6	19.8	18.9	18.0	18.0	16.2	15.3	14.4	12.6	11.7
77.5°	15.3	14.4	13.5	12.6	12.6	11.7	10.8	9.9	9.0	8.1	6.3
80°	9.9	9.0	8.1	8.1	7.2	7.2	6.3	5.4	4.5	3.6	2.7
82.5°	5.4	5.4	4.5	3.6	3.6	3.6	2.7	2.7	1.8	0.9	0.9
85°	1.8	1.8	1.8	1.8	0.9	0.9	0.9	0.9	0.9	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P642288

CATALOG NUMBER: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3
2.5°	272.3	272.3	272.3	272.3	272.3	272.3	271.4	272.3	272.3	272.3	271.4
5°	271.4	270.5	270.5	271.4	270.5	270.5	271.4	271.4	271.4	270.5	270.5
7.5°	267.8	268.7	267.8	267.8	268.7	268.7	268.7	268.7	267.8	267.8	268.7
10°	265.1	265.1	264.2	265.1	264.2	265.1	265.1	265.1	265.1	265.1	265.1
12.5°	260.6	260.6	260.6	261.5	260.6	260.6	261.5	261.5	261.5	261.5	261.5
15°	255.2	255.2	256.1	255.2	256.1	256.1	256.1	256.1	256.1	256.1	257.0
17.5°	249.8	249.8	249.8	249.8	249.8	249.8	249.8	249.8	249.8	250.7	250.7
20°	243.5	243.5	243.5	243.5	243.5	242.6	243.5	243.5	244.4	244.4	244.4
22.5°	235.5	235.5	235.5	235.5	235.5	235.5	235.5	235.5	236.4	237.3	236.4
25°	227.4	227.4	227.4	227.4	227.4	227.4	227.4	228.3	228.3	228.3	229.2
27.5°	219.3	219.3	219.3	218.4	219.3	218.4	219.3	219.3	220.2	219.3	220.2
30°	210.3	209.4	209.4	209.4	209.4	210.3	209.4	209.4	210.3	211.2	210.3
32.5°	198.6	198.6	198.6	199.5	199.5	199.5	200.4	199.5	199.5	200.4	200.4
35°	187.8	187.8	187.8	188.7	188.7	188.7	188.7	189.6	189.6	189.6	190.5
37.5°	176.1	177.0	176.1	177.0	177.0	177.9	177.9	177.9	177.9	178.8	178.8
40°	165.4	164.5	165.4	165.4	165.4	165.4	165.4	165.4	166.3	167.2	167.2
42.5°	152.8	152.8	152.8	152.8	152.8	152.8	153.7	153.7	153.7	154.6	154.6
45°	140.2	139.3	139.3	139.3	139.3	140.2	139.3	140.2	140.2	141.1	141.1
47.5°	126.7	126.7	126.7	126.7	126.7	126.7	126.7	126.7	126.7	127.6	126.7
50°	115.0	114.1	113.2	113.2	112.3	113.2	112.3	112.3	112.3	113.2	112.3
52.5°	101.6	100.7	99.8	99.8	99.8	98.9	98.0	98.0	98.0	97.1	97.1
55°	89.9	89.0	87.2	88.1	86.3	85.4	85.4	84.5	83.6	83.6	82.7
57.5°	77.3	76.4	75.5	74.6	74.6	72.8	71.9	71.0	70.1	69.2	67.4
60°	66.5	64.7	62.9	62.9	62.0	61.1	59.3	57.5	56.6	54.8	53.9
62.5°	54.8	53.0	51.2	50.3	49.4	48.5	46.7	44.9	43.1	42.2	40.4
65°	44.0	42.2	40.4	39.5	38.6	36.8	35.0	33.3	31.5	29.7	28.8
67.5°	33.3	31.5	30.6	28.8	27.9	26.1	24.3	23.4	21.6	19.8	17.1
70°	24.3	22.5	20.7	19.8	18.9	17.1	16.2	14.4	12.6	11.7	9.9
72.5°	16.2	14.4	13.5	12.6	11.7	10.8	9.0	8.1	6.3	5.4	4.5
75°	9.9	9.0	8.1	7.2	6.3	5.4	4.5	3.6	2.7	1.8	0.9
77.5°	5.4	4.5	3.6	3.6	2.7	1.8	1.8	0.9	0.9	0.9	0.9
80°	2.7	1.8	0.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.9
82.5°	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P642288

CATALOG NUMBER: ML5612LSWW97FS1E - 592SC WW - 600LM - 3500K

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3
2.5°	272.3	272.3	272.3	272.3	272.3	272.3	272.3	272.3
5°	271.4	271.4	270.5	271.4	270.5	270.5	270.5	271.4
7.5°	268.7	268.7	268.7	268.7	268.7	268.7	268.7	268.7
10°	265.1	265.1	265.1	266.0	266.0	266.0	265.1	266.0
12.5°	261.5	261.5	261.5	262.4	261.5	262.4	261.5	262.4
15°	257.0	257.0	257.9	257.9	257.0	257.0	257.9	257.9
17.5°	250.7	251.6	251.6	251.6	251.6	251.6	251.6	252.5
20°	245.3	245.3	244.4	245.3	245.3	246.2	246.2	245.3
22.5°	236.4	238.2	238.2	238.2	238.2	238.2	238.2	238.2
25°	229.2	229.2	229.2	230.1	229.2	229.2	230.1	229.2
27.5°	220.2	221.1	220.2	221.1	221.1	221.1	221.1	221.1
30°	211.2	211.2	211.2	211.2	211.2	212.1	211.2	211.2
32.5°	200.4	201.3	201.3	201.3	202.2	201.3	201.3	202.2
35°	190.5	190.5	190.5	191.4	190.5	191.4	191.4	190.5
37.5°	178.8	179.7	178.8	179.7	179.7	179.7	179.7	179.7
40°	168.1	167.2	168.1	167.2	168.1	168.1	168.1	167.2
42.5°	154.6	155.5	155.5	155.5	155.5	155.5	155.5	154.6
45°	141.1	142.0	142.0	142.0	142.0	142.0	142.9	142.9
47.5°	126.7	128.5	128.5	128.5	127.6	129.4	128.5	128.5
50°	112.3	112.3	113.2	113.2	114.1	114.1	114.1	114.1
52.5°	98.0	97.1	98.0	98.0	98.9	98.0	98.9	98.0
55°	81.8	81.8	81.8	80.9	81.8	81.8	81.8	81.8
57.5°	67.4	66.5	65.6	64.7	64.7	64.7	63.8	64.7
60°	52.1	50.3	51.2	49.4	48.5	47.6	47.6	46.7
62.5°	38.6	36.8	35.9	35.0	33.3	31.5	31.5	30.6
65°	26.1	24.3	23.4	21.6	20.7	19.8	18.9	18.9
67.5°	16.2	14.4	14.4	13.5	12.6	11.7	10.8	10.8
70°	9.0	8.1	7.2	6.3	6.3	5.4	4.5	4.5
72.5°	3.6	2.7	2.7	1.8	1.8	1.8	1.8	0.9
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)