

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641802

Luminaire Tested: ML5612LSVWFL97FS1E - 692W - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-108)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 692W - 1200LM - 3000K
Description: ML56 RR, MILKY OPTIC, 6" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1376.1 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641802
CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641802

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89																			
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79																			
3	96	88	81	76	94	87	80	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63																			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	53	48	59	53	48	58	52	48	57	51	47	46																			
8	69	57	49	44	67	56	49	44	55	48	44	54	48	44	53	47	43	42																			
9	64	52	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	59	48	42	37	47	41	37	47	41	37	46	40	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43302
5°	43094
10°	42529
15°	41822
20°	40924
25°	39885
30°	38468
35°	36667
40°	32590
45°	24661
50°	16810
55°	11565
60°	8651
65°	7225
70°	6540
75°	6037
80°	5146
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24661 cd/sqm



TEST NUMBER: P641802

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	5.4
10°-20°	207.5	15.1
20°-30°	302.9	22.0
30°-40°	338.3	24.6
40°-50°	246.2	17.9
50°-60°	113.2	8.2
60°-70°	56.5	4.1
70°-80°	29.8	2.2
80°-90°	7.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.5	42.5
0°-40°	922.8	67.1
0°-60°	1282.2	93.2
0°-90°	1376.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1376.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	790	
5°	783	74
15°	737	207
25°	659	303
35°	548	338
45°	318	246
55°	121	113
65°	56	56
75°	28	30
85°	7	8
90°	0	



TEST NUMBER: P641802

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692W - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	789.9
2.5°	787.2
5°	783.1
7.5°	774.9
10°	764.0
12.5°	751.8
15°	736.9
17.5°	719.2
20°	701.5
22.5°	681.1
25°	659.4
27.5°	633.5
30°	607.7
32.5°	579.2
35°	547.9
37.5°	507.1
40°	455.4
42.5°	390.2
45°	318.1
47.5°	251.5
50°	197.1
52.5°	153.6
55°	121.0
57.5°	96.5
60°	78.9
62.5°	65.3
65°	55.7
67.5°	47.6
70°	40.8
72.5°	34.0
75°	28.5
77.5°	21.8
80°	16.3
82.5°	10.9
85°	6.8
87.5°	2.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)