

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641836

Luminaire Tested: ML5612LSVWFL97FS1E - 693SNB - 600LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641836  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-111)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 693SNB - 600LM - 2700K  
Description: ML56 RR, MILKY OPTIC, 6" SATIN NICKLE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 769.9 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641836  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 693SNB - 600LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641836

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693SNB - 600LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	69	76	72	69	67																			
5	86	76	69	64	85	75	69	64	73	68	63	72	67	63	70	66	62	60																			
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55																			
7	76	65	58	53	74	64	57	53	63	57	52	61	56	52	60	55	52	50																			
8	71	60	53	48	70	59	53	48	58	52	48	57	52	47	56	51	47	46																			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	43	42																			
10	63	52	45	41	62	51	45	40	50	44	40	50	44	40	49	44	40	39																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27317
5°	27190
10°	26747
15°	26209
20°	25500
25°	24739
30°	23738
35°	22366
40°	19594
45°	14242
50°	8554
55°	4635
60°	2335
65°	999
70°	272
75°	191
80°	284
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14242 cd/sqm



TEST NUMBER: P641836

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693SNB - 600LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.7	6.1
10°-20°	129.9	16.9
20°-30°	187.9	24.4
30°-40°	206.5	26.8
40°-50°	141.5	18.4
50°-60°	46.9	6.1
60°-70°	8.7	1.1
70°-80°	1.3	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.6	47.4
0°-40°	571.1	74.2
0°-60°	759.6	98.7
0°-90°	769.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	769.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	498	
5°	494	47
15°	462	130
25°	409	188
35°	334	207
45°	184	142
55°	48	47
65°	8	9
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641836

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693SNB - 600LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	498.3
2.5°	497.5
5°	494.1
7.5°	488.1
10°	480.5
12.5°	472.0
15°	461.8
17.5°	449.9
20°	437.1
22.5°	423.5
25°	409.0
27.5°	392.9
30°	375.0
32.5°	356.3
35°	334.2
37.5°	307.8
40°	273.8
42.5°	231.3
45°	183.7
47.5°	138.6
50°	100.3
52.5°	70.6
55°	48.5
57.5°	32.3
60°	21.3
62.5°	12.8
65°	7.7
67.5°	3.4
70°	1.7
72.5°	1.7
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)