

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641839

Luminaire Tested: ML5612LSVWFL97FS1E - 693SNB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-111)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 693SNB - 600LM - 4000K
Description: ML56 RR, MILKY OPTIC, 6" SATIN NICKLE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 875.1 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641839
CATALOG NUMBER: ML5612LSVWFL97FS1E - 693SNB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641839

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693SNB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 94 | 93 | 91 | | | 91 |
| 2 | 105 | 100 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 91 | 88 | 92 | 89 | 86 | 89 | 86 | 84 | 82 | | | 82 |
| 3 | 99 | 91 | 85 | 80 | 97 | 90 | 84 | 80 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 74 | | | 74 |
| 4 | 92 | 83 | 77 | 72 | 90 | 82 | 76 | 71 | 80 | 75 | 70 | 78 | 73 | 69 | 76 | 72 | 69 | 67 | | | 67 |
| 5 | 86 | 76 | 69 | 64 | 85 | 75 | 69 | 64 | 73 | 68 | 63 | 72 | 67 | 63 | 70 | 66 | 62 | 60 | | | 60 |
| 6 | 81 | 70 | 63 | 58 | 79 | 69 | 63 | 58 | 68 | 62 | 57 | 66 | 61 | 57 | 65 | 60 | 57 | 55 | | | 55 |
| 7 | 76 | 65 | 58 | 53 | 74 | 64 | 57 | 53 | 63 | 57 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 50 | | | 50 |
| 8 | 71 | 60 | 53 | 48 | 70 | 59 | 53 | 48 | 58 | 52 | 48 | 57 | 52 | 47 | 56 | 51 | 47 | 46 | | | 46 |
| 9 | 67 | 56 | 49 | 44 | 66 | 55 | 49 | 44 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 47 | 43 | 42 | | | 42 |
| 10 | 63 | 52 | 45 | 41 | 62 | 51 | 45 | 40 | 50 | 44 | 40 | 50 | 44 | 40 | 49 | 44 | 40 | 39 | | | 39 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 31056 |
| 5° | 30910 |
| 10° | 30405 |
| 15° | 29790 |
| 20° | 28988 |
| 25° | 28127 |
| 30° | 26985 |
| 35° | 25424 |
| 40° | 22277 |
| 45° | 16188 |
| 50° | 9731 |
| 55° | 5266 |
| 60° | 2653 |
| 65° | 1129 |
| 70° | 305 |
| 75° | 212 |
| 80° | 316 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16188 cd/sqm



TEST NUMBER: P641839

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693SNB - 600LM - 4000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 53.1 | 6.1 |
| 10°-20° | 147.7 | 16.9 |
| 20°-30° | 213.7 | 24.4 |
| 30°-40° | 234.8 | 26.8 |
| 40°-50° | 160.9 | 18.4 |
| 50°-60° | 53.3 | 6.1 |
| 60°-70° | 9.8 | 1.1 |
| 70°-80° | 1.4 | 0.2 |
| 80°-90° | 0.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 414.5 | 47.4 |
| 0°-40° | 649.3 | 74.2 |
| 0°-60° | 863.5 | 98.7 |
| 0°-90° | 875.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 875.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 566 | |
| 5° | 562 | 53 |
| 15° | 525 | 148 |
| 25° | 465 | 214 |
| 35° | 380 | 235 |
| 45° | 209 | 161 |
| 55° | 55 | 53 |
| 65° | 9 | 10 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P641839

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693SNB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 566.5 |
| 2.5° | 565.5 |
| 5° | 561.7 |
| 7.5° | 554.9 |
| 10° | 546.2 |
| 12.5° | 536.5 |
| 15° | 524.9 |
| 17.5° | 511.4 |
| 20° | 496.9 |
| 22.5° | 481.4 |
| 25° | 465.0 |
| 27.5° | 446.6 |
| 30° | 426.3 |
| 32.5° | 405.1 |
| 35° | 379.9 |
| 37.5° | 350.0 |
| 40° | 311.3 |
| 42.5° | 263.0 |
| 45° | 208.8 |
| 47.5° | 157.6 |
| 50° | 114.1 |
| 52.5° | 80.2 |
| 55° | 55.1 |
| 57.5° | 36.7 |
| 60° | 24.2 |
| 62.5° | 14.5 |
| 65° | 8.7 |
| 67.5° | 3.9 |
| 70° | 1.9 |
| 72.5° | 1.9 |
| 75° | 1.0 |
| 77.5° | 1.0 |
| 80° | 1.0 |
| 82.5° | 1.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)