

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641849

Luminaire Tested: ML5612LSVWFL97FS1E - 693TBZB - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641849
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-112)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 693TBZB - 1200LM - 4000K
Description: ML56 RR, MILKY OPTIC, 6" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1221.7 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.21
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641849
CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641849

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	69	76	72	69	67																			
5	86	76	69	64	85	75	69	64	73	68	63	72	67	63	70	66	62	60																			
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55																			
7	76	65	58	53	74	64	57	52	63	57	52	61	56	52	60	55	52	50																			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46																			
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42																			
10	63	52	45	40	62	51	45	40	50	44	40	50	44	40	49	44	40	38																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41921
5°	41833
10°	41393
15°	40840
20°	40143
25°	39347
30°	38227
35°	36292
40°	31931
45°	22832
50°	13322
55°	7034
60°	3289
65°	1362
70°	481
75°	318
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22832 cd/sqm



TEST NUMBER: P641849

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	5.9
10°-20°	202.9	16.6
20°-30°	299.1	24.5
30°-40°	334.9	27.4
40°-50°	227.1	18.6
50°-60°	72.1	5.9
60°-70°	12.1	1.0
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.0	47.0
0°-40°	908.9	74.4
0°-60°	1208.0	98.9
0°-90°	1221.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1221.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	765	
5°	760	72
15°	720	203
25°	650	299
35°	542	335
45°	294	227
55°	74	72
65°	10	12
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P641849

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	764.7
2.5°	763.2
5°	760.2
7.5°	752.7
10°	743.6
12.5°	733.1
15°	719.6
17.5°	706.1
20°	688.1
22.5°	670.0
25°	650.5
27.5°	628.0
30°	603.9
32.5°	576.9
35°	542.3
37.5°	500.3
40°	446.2
42.5°	374.1
45°	294.5
47.5°	219.3
50°	156.2
52.5°	109.7
55°	73.6
57.5°	49.6
60°	30.0
62.5°	18.0
65°	10.5
67.5°	4.5
70°	3.0
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)